

# ClickShare Hub Pro + Huddly® C1™ room system

Microsoft Teams Room bundle for enhanced collaboration in small-to-medium-sized meeting rooms.



- **Wireless presentation: 4K content sharing with 2 next-gen ClickShare Buttons with USB-C DisplayPort™**
- **Built on the Microsoft Device Ecosystem platform (MDEP)**
- **Dual display support**
- **AI-driven Huddly video bar that scales from standalone to multi-camera, also certified with the Hub Core**

The ClickShare Hub Pro and Huddly® C1™ bundle is a Microsoft Teams Rooms solution for small-to-medium-sized rooms. ClickShare Hub Pro enables one-click wireless conferencing and 4K content sharing with two next-gen ClickShare Buttons featuring Wi-Fi 6E and USB-C DisplayPort™, plus dual-screen support.

The Huddly® C1™ is a modular, AI-driven video bar that scales from standalone to multi-camera. It brings unparalleled flexibility, premium video, and intelligent audio, for truly engaging meetings.

## Product specifications

## CLICKSHARE HUB PRO + HUDDLY® C1™ ROOM SYSTEM

### General specifications

Operating system	Android (MDEP)
Microsoft Teams Rooms license required	Yes
System requirements	For ClickShare App. Minimum: Intel Core i3 or AMD Ryzen 5, 8GB RAM, Windows 10 20H5; Intel Core i3 or Apple Silicon M1, 8GB RAM, macOS 11 Big Sur Recommended: Intel Core i5/Ultra 5 or AMD Ryzen 7, 8GB RAM, Windows 11 latest build; Apple Silicon M3, 8GB RAM, macOS latest build
Video outputs	HDMI-1: UWSK WUHD (5120*2160) @30Hz HDMI 2.0 HDMI-2: 4K UHD (3840*2160) @30Hz HDMI 2.0 eDP (Control Panel): HD (1280*800) @60Hz DP 1.4
Video inputs	4K UHD (3840*2160) @30Hz HDMI 2.0
Camera	Huddly C1 video bar camera with 150° lens
Audio output	USB-A 2.0/3.0 USB-C 2.0/3.0 HDMI 2.0
ClickShare Buttons	2 ClickShare Buttons 5th Generation
Microphones	16 smart microphones
ClickShare App	Desktop
Speakers	Hi-fi stereo speakers
Noise Level	Maximum 25 dBA @ 30°C
Wireless transmission protocol	IEEE 802.11 a/b/g/n/ac/ax/be and IEEE 802.15.1 BT 5.3
Reach	Max. 30m (100ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4GHz, 5GHz and 6GHz DBS/HBS (DFS channels supported in select number of countries)
Connections	Back: 1x Ethernet LAN 1Gbit 1x USB-C Power delivery 3.1 EPR (for power adapter) 2x HDMI 2.0 output 2x USB-C 2.0/3.0 1x USB-A 2.0/3.0 1x USB-C 2.0/3.0 Device + USB-C DisplayPort™ output 1x USB-C 2.0 + USB-C DisplayPort™ output Front: 1x USB-C 2.0/3.0
Temperature range	Operating: 0°C + 40°C (+32°F to +104°F) Max 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Network connection	LAN
Management and reporting	Yes, XMS Cloud
Warranty	3 years
Dimensions (HxWxD)	37 * 180 * 180 (mm)
Power consumption	Operational: 160W (max) Standby:
Power supply	External USB-C charger 100W (PD3.0 SPR), 180W (PD3.1 EPR)
Weight	720gr

### ClickShare 10M 20W USB-C AOC Cable (Directional)

Cable Length / Diameter	A0M / 6mm
Interface	USB Type-C 3.2 Gen1, DP 1.4
Power Delivery	20W
Bend Radius	60mm/30mm (Fixed/Temporarily) While a minimum bend of 30mm is acceptable during handling or routing, it must not be maintained as a permanent fixture
Temperature range	Operating: -10°C + 60°C (+14°F to +140°F) Storage: -20°C to +70°C (-4°F to +158°F)
Humidity	Storage/Operation: 0 to 85% relative humidity, non-condensing
Flame rated	VW-1 (Not plenum rated)

### Power supply

AC Input	100-240V~50-60Hz 1.4A
DC Output	100W max (20V 5A) / 45W (15V 3A) / 36W (12V 3A) / 27W (9V 3A) / 15W (5V 3A)
Output Plug	USB Type-C
Input AC Type	IEC60320-C6
Energy Efficiency Level	Comply with DOE standard Level VI
Altitude	5,000 meters
DC cable length	1.5m

### Power cord

Color	Black
Length	0.5m
Plug Type	EU / US / UK / CN / CH / IN / ZA / ANZ
Connector Type	IEC60320-C5

### Control Panel

Touchscreen	10.1-inch projected capacitive touchscreen with anti-fingerprint and anti-glare coatings, supporting up to 4 touch points for enhanced visibility and durability
Resolution	1280*800 @60Hz
Brightness	300 nits
Contrast ratio	1000:1
Viewing angle	80° (Up/Down/Left/Right)
Human detection sensor	Automatically detects in-room human movement within a 2-meter range and 90° field of view to wake the system.
Connections	USB Type-C 2.0, DisplayPort Alt Mode, PD3.0 Recommend using the included ClickShare 10M USB-C AOC cable for optimal performance
Anti-theft system	Kensington lock
Temperature range	Operating: 0°C + 40°C (+32°F to +104°F) Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Dimensions (HxWxD)	254.5 x 187.9 x 76.9 (mm)
Power consumption	Powered over USB from connected Base Unit Operational: 7.3W (max) Standby:

Last updated: 21 May 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.