

Bragi

Using Barco's renowned Pulse electronic and software platform, Bragi is powered by a revolutionary, new, high lumens density (HLD) RGB LED light engine.



- Theater Series
- 4K UHD Resolution (3,840 x 2,160)
- Solid State RGB LED
- Up to 2,600 ANSI Lumens

Bragi takes its name from an historical ninth-century poet. His poems were so outstandingly artful and moving that subsequent generations imagined that, upon his death, Odin had appointed him the court poet of Valhalla.

Bragi, being Balder's brother and inherits the same design philosophy, optical core and lenses.

State of the art electronics

Our Pulse electronics are built on a superior FPGA platform featuring a dual core processor on the industry's only 20 nm SoC, with 96 transceiver lanes delivering 3.3Tbps of serial bandwidth.

Thanks to our unique single step processing technology (SSPTM), Pulse electronics are designed to process 4K UHD, HDMI™ 2.0a, HDCP 2.2 and HDR10 signals with extremely low latency.

Bragi uses the very latest 0.9" DMD DLP chipset, to display flawless 4K UHD (3,840 x 2,160 px) images.

LED Engine

Bragi uses a new optical engine, incorporating the best elements from previous models and combining them with new technologies, creating an even better optical engine.

Bragi's optical engine is not the only part that is redesigned, the light source is brand new, and this time it's not laser. The light source uses the very latest high lumens density (HLD), LED illumination technology.

HLD LED is unique in that it works around the 'law of etendue' (a property of light in an optical system, which characterizes how "spread out" the light is in area and angle...) to deliver a superb color experience and incredible brightness while enabling new levels of resolution.

RealColor

Combining HLD LED illumination with regular LED colors which appear more saturated, the human eye is tricked to interpret this as richer, brighter colors than they are physically measured. Bragi also includes a motorized DCI/P3 filter for improved HDR color accuracy.

Additionally, Barco's RealColor processing enables simple and accurate calibration to your desired color gamut or white point.

Product specifications**BRAGI****General specifications**

| | |
|-----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Projector type | Single chip DLP |
| Light source lifetime | Up to 50,000 hours * Brightness mode dependent |
| CLO (constant light output) | Yes |
| Optical dowser | Yes |
| Technology | 0.9" DMD™ |
| Integrated web server | Yes |
| Resolution | 3,840 x 2,160 (4K UHD) |
| Diagnostics | via Prospector web interface |
| Aspect ratio | 1.78:1 |
| Light source | Solid State RGB LED |
| Light output | Up to 2,600 ANSI Lumens |
| Contrast ratio | 1,800:1 Sequential 450:1 ANSI |
| Brightness uniformity | >90% |
| Input resolutions | From VGA up to 4K UHD (3,840 x 2,160) @ 60Hz or up to 2,560 x 1,600 @ 120Hz |
| Lens range | (R9802232) -EN68 (0.30:1) -Periscope Lens (requires vertical installation) (R9801832) -FLDX UST (0.41:1) -90° Lens (R9802244) -EN67 (0.65:1) (R9802243) -EN66 (0.80 -1.21:1) (R9802003) -EN76 (0.95 -1.30:1) (R9802242) -EN63 (1.20 -1.70:1) * (R9802241) -EN61 (1.70 -2.50:1) * (R9801211) -EN44 (2.50 -4.60:1) *Standard Lens Option(s) |
| Optical lens shift | Up to 88% vertical lens shift & up to 38% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here |
| Color correction | P7 RealColor™ |
| Color gamut | REC.709 DCI (P3) via internal filter |
| Image processing | Embedded Warp & Blend Engine |
| WARP | 4-Corner Warp & Bow Correction via Warp Engine |
| Orientation | 360° Rotation |
| Network connection | 10/100 Ethernet via RJ45 connection |
| HDR | HDR10 |
| 3D | Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details |

Product specifications**BRAGI**

| | |
|-------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Inputs | 1 x HDMITM 2.0 (HDCP 2.2) 1 x HDBaseT (HDCP 1.4 -9Gbps only) 2 x Dual Link DVI-D 2 x Display Port (1.2) 12G-SDI 1 x RJ45 Ethernet 1 x RS232 1 x Remote Control (RC) 3 x USB (2 x Rear, 1 x Front) DMX (1 x Input, 1 x Output) |
| Shipping Dimensions | Excluding lens 464 x 679 x 773 mm 18.27 x 26.7 x 30.4 in |
| Control | IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant NOTE: 12v Trigger(s) do not follow standard functionality, and require an IP command to enable / disable them. Download our integration guide for more information. |
| Shipping weight | TBC |
| Power requirements | 100 -240V / 50 -60Hz |
| Standard accessories | Power Cord, Remote Control |
| Certifications | CE, FCC Class A and cCSAus |
| Power consumption | 570 W -Max |
| Noise level (typical at 25°C/77°F) | 30 -33 dB(A) Max |
| 24/7 operation | This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications. |
| Operating temperature | 10 to 45 °C at Sea Level Optimal Set Point: 20 °C |
| Operating humidity | 20 to 80% (relative humidity) |
| * | * Service required following 20,000 hours use Please contact an authorized Barco representative for details |
| BTU per hour | 1,945 BTU/h -Max |
| Airflow requirements | Air Inlet (from Rear w/Feet Down): Right Side Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 1cm Left: 1cm Right: 25cm Rear: 25cm Top: 1cm |
| Exhaust airflow | 58 ft ³ /min @ 22.9 °C 99 m ³ /hour @ 22.9 °C Download Lens & Airflow Data Here |
| Dimensions (WxLxH) | Excluding lens 450 x 482 x 255 mm 17.7 x 19 x 10 in. |
| Weight | Excluding lens 21.5 kg / 47.4 lbs |
| Warranty | Limited 3 years parts and labor Extendable up to 5 years |

Last updated: 21 May 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.