

# ClickShare Hub Pro + Huddly ® L1™ + Shure room system

Microsoft Teams Room bundle for enhanced collaboration in medium-to-large-sized meeting rooms.

- **Wireless presentation: 4K content sharing with 2 next-gen ClickShare Buttons with USB-C DisplayPort™**
- **Wireless BYOD for Microsoft Teams Rooms to run other videoconferencing platforms (Zoom, WebEx, Google Meet, etc.)**
- **Built on the Microsoft Device Ecosystem platform (MDEP)**
- **Dual display support**
- **Huddly® L1™ 6K camera with built-in AI director for visually engaging meetings**
- **Shure MXA902 ceiling array microphone and**

The ClickShare Hub Pro, Huddly, and Shure bundle is a Microsoft Teams Rooms solution for medium-to-large meeting rooms. ClickShare Hub Pro enables effortless one-click wireless conferencing and 4K content sharing with two next-gen ClickShare Buttons (featuring Wi-Fi 6E and USB-C DisplayPort™) and dual-screen support.

The Huddly® L1™ delivers engaging video collaboration with an on-device AI director and exceptional image quality. The Shure MXA902 ceiling array microphone and loudspeaker with the ANIUSB-MATRIX USB audio network interface provide top-quality audio.

## Technische Daten

## CLICKSHARE HUB PRO + HUDDL® L1™ + SHURE ROOM SYSTEM

### Allgemeine Daten

Betriebssystem	Android (MDEP)
Microsoft Teams Rooms license required	Yes
Systemanforderungen	For ClickShare App. Minimum: Intel Core i3 or AMD Ryzen 5, 8GB RAM, Windows 10 20H5; Intel Core i3 or Apple Silicon M1, 8GB RAM, macOS 11 Big Sur Recommended: Intel Core i5/Ultra 5 or AMD Ryzen 7, 8GB RAM, Windows 11 latest build; Apple Silicon M3, 8GB RAM, macOS latest build
Videoausgänge	HDMI-1: UWSK WUHD (5120*2160) @30Hz HDMI 2.0 HDMI-2: 4K UHD (3840*2160) @30Hz HDMI 2.0 eDP (Control Panel): HD (1280*800) @60Hz DP 1.4
Videoeingänge	4K UHD (3840*2160) @30Hz HDMI 2.0
Kamera	Huddly® L1™ 6K conference camera with next-generation AI functionality, including industry-leading smart framing and advanced room analytics
Audioausgang	USB-A 2.0/3.0 USB-C 2.0/3.0 HDMI 2.0
ClickShare Buttons	2 ClickShare Buttons 5th Generation
Mikrofone	MXA902 Ceiling Array Microphone + Loudspeaker: Single Zone Automatic Coverage™ technology to capture audio from a 20 by 20 foot (6 by 6 meter) area out of the box and integrated 2.5-inch wide-dispersion loudspeaker for clear, intelligible speech reproduction ANIUSB-MATRIX USB Audio Network Interface with Matrix Mixing: Connects 4 Dante audio inputs and 1 analog input to an A / V conferencing system or a PC-based videoconferencing application
ClickShare-App	Desktop
Geräuschpegel	Maximum 25 dBA @ 30°C
Drahtloses Übertragungsprotokoll	IEEE 802.11 a/b/g/n/ac/ax/be and IEEE 802.15.1 BT 5.3
REACH	Max. 30m (100ft) between ClickShare Button and ClickShare Base Unit
Frequenzband	2.4GHz, 5GHz and 6GHz DFS/HSS (DFS channels supported in select number of countries)
Anschlüsse	Back: 1x Ethernet LAN 1Gbit 1x USB-C Power delivery 3.1 EPR (for power adapter) 2x HDMI 2.0 output 2x USB-C 2.0/3.0 1x USB-A 2.0/3.0 1x USB-C 2.0/3.0 Device + USB-C DisplayPort™ output 1x USB-C 2.0 + USB-C DisplayPort™ output Front: 1x USB-C 2.0/3.0
Temperaturbereich	Operating: 0°C + 40°C (+32°F to +104°F) Max 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Luftfeuchtigkeit	Storage/Operation: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Diebstahlsicherung	Kensington lock
Zertifizierungen	FCC/CE
Netzwerkverbindung	LAN
Verwaltung und Berichterstellung	Yes, XMS Cloud
Garantie	3 years
Abmessungen (HxBxT)	37 * 180 * 180 (mm)
Leistungsaufnahme	Operational: 160W (max) Standby:
Stromversorgung	External USB-C charger 100W (PD3.0 SPR), 180W (PD3.1 EPR)
Gewicht	720gr

### ClickShare 10M 20W USB-C AOC Cable (Directional)

Cable Length / Diameter	A0M / 6mm
Interface	USB Type-C 3.2 Gen1, DP 1.4
Power Delivery	20W
Bend Radius	60mm/30mm (Fixed/Temporarily) While a minimum bend of 30mm is acceptable during handling or routing, it must not be maintained as a permanent fixture
Temperature range	Operating: -10°C + 60°C (+14°F to +140°F) Storage: -20°C to +70°C (-4°F to +158°F)
Humidity	Storage/Operation: 0 to 85% relative humidity, non-condensing
Flame rated	VW-1 (Not plenum rated)

### Power supply

AC Input	100-240V~50-60Hz 1.4A
DC Output	100W max (20V 5A) / 45W (15V 3A) / 36W (12V 3A) / 27W (9V 3A) / 15W (5V 3A)
Output Plug	USB Type-C
Input AC Type	IEC60320-C6
Energy Efficiency Level	Comply with DOE standard Level VI
Altitude	5,000 meters
DC cable length	1.5m

### Power cord

Color	Black
Length	0.5m
Plug Type	EU / US / UK / CN / CH / IN / ZA / ANZ
Connector Type	IEC60320-C5

### Control Panel

Touchscreen	10.1-inch projected capacitive touchscreen with anti-fingerprint and anti-glare coatings, supporting up to 4 touch points for enhanced visibility and durability
Resolution	1280*800 @60Hz
Brightness	300 nits
Contrast ratio	1000:1
Viewing angle	80° (Up/Down/Left/Right)
Human detection sensor	Automatically detects in-room human movement within a 2-meter range and 90° field of view to wake the system.
Connections	USB Type-C 2.0, DisplayPort Alt Mode, PD3.0 Recommend using the included ClickShare 10M USB-C AOC cable for optimal performance
Anti-theft system	Kensington lock
Temperature range	Operating: 0°C + 40°C (+32°F to +104°F) Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Dimensions (HxWxD)	254.5 x 187.9 x 76.9 (mm)
Power consumption	Powered over USB from connected Base Unit. Operational: 7.3W (max) Standby:

Generiert am: 15 Jun 2026

© 2026 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter [www.barco.com](http://www.barco.com).

[www.barco.com](http://www.barco.com)

**BARCO**