

G100-W22

22,000 lumen, WUXGA, single-chip laser phosphor projector



- **single-chip high-brightness projections**
- **up-to-date input capabilities & future-proof design**
- **full operational flexibility through wide lens range**

100% image performance

The G100 series opens up the possibilities of our single-chip offering with higher brightness levels than before. It brings great image quality with an impressive lumens power for bright projections indoor and outdoor. What's more, the G100 supports all the latest input sources, including HDMI™ 2.0, to assure deep color palettes and qualitative projections.

Thanks to Barco's Projector Toolset software, installing and managing your projector(s) can be done from the comfort of your own computer with the intuitive user interface. In addition, the Ptoolset blending and warping capabilities, make these projectors a perfect fit for multi-channel media-based attractions like planetariums, domes, theatres and projection mappings.

100% flexibility

To enable full operational versatility and effortless implementation in different project designs, the G100 comes with a stable lens holder to guarantee reliable blending and non-moving images in multi-channel set-ups, and a new extensive GC-lens range supporting a throw ratio going from 0.38 up to a 10.8. It gives you flexibility to shoot from long/and or short distances, and to play with 360° orientation possibilities. The projector and its peripherals deliver the best outcomes for any creative project.

With the excellent onboard cooling the G100s can withstand a maximum ambient operating temperature of 50°C (122°F), and this all only at max. 42 dB noise levels.

100% reliability

Through its laser-phosphor light source and advanced cooling design, the G100 provides a long operating time (> 20.000 hrs) without need for lamp changes -resulting in considerable cost-savings on maintenance and consumables.

With its up-to-date and future-proof design the G100 is built to meet all your requirements in terms of image quality, reliability and sustainability.

Product specificaties**G100-W22****Algemene specificaties**

Projectortype	Single chip DLP laser phosphor projector
Resolutie	1,920 x 1,200 (WUXGA) -0.96" DLP chip
Helderheid	22,000 ISO lumen / 20,600 center lumen / 18,500 ANSI lumen 23,750 ISO lumen (Super Bright mode)*
Uniformiteit van de helderheid	90%
Contrastverhouding	1,100:1 sequential; 5,500:1 dynamic; Extreme black: 100,000:1
Lichtbron	Laser phosphor
Levensduur lichtbron	Up to 20,000hrs
Aspectverhouding	16:10
Oriëntatie	360° rotation, no restrictions
Verzegelde DLP™ core	Yes
Kleurcorrectie	Yes
CLO (constante lichtopbrengst)	Yes
Keystone-correctie	Yes
Beeldverwerking	Embedded warp & blend. Also available via Projector Toolset
3D	Active and passive stereoscopic 3D
Type lens	GC lenses -0.65-0.75:1 / 0.84-1.02:1 / 1.02-1.36:1 / 1.2-1.5:1 / 1.5-2.0:1 / 2.0-4.0:1 / 4.0-7.2:1 / 7.2-10.8:1 FLDX lens -0.38 : 1 UST 90°
Optische lensverschuiving	Vertical up to 120%, depending on lens Horizontal up to 50%, depending on lens Motorized zoom and focus Motorized lens shift
Ingangen	2x HDMI™ 2.0b / DisplayPort 1.2a / DVI-D / HDBaseT / 3G-SDI / VGA (D-Sub 15 pin)
Invoerresolutie	Up to 4K UHD @60Hz Refresh rates: 24Hz to 60Hz for WUXGA and 4KUHD (4096 x 2160 / 3840 x 2160) 4K input signals will be scaled to the projector's output resolution
Software-instrumenten	Projector Toolset
Bediening	IR, RS232, RJ45, USB type A
Netwerkverbinding	10/100 Ethernet, RJ45
Stroomvereisten	100-240V / 50-60Hz
Stroomverbruik	1200W nominal, 1380W maximum (@220V)
Stand-by vermogen	less than 0.5W
BTU per uur	4095 BTU/h minimal, 4710 BTU/h maximum (@220V)
Geluidsniveau (typisch bij 25°C/77°F)	38dB(A) -42dB(A) depending on the used mode
Temperatuur tijdens gebruik	0 -50 °C (sea level)
Luchtvochtigheid tijdens gebruik	10 -85% RH, non-condensing
Temperatuur bij opslag	-10 to 60 °C
Luchtvochtigheid bij opslag	5 -90% RH, non-condensing
Afmetingen (BxLxH)	without feet: 650 x 710 x 251 mm / 25.6 x 27.9 x 9.9 in
Gewicht	without lens: 54 kg / 119.0 lbs
Standaard accessoires	Power cord, wireless remote control
Certificeringen	CE, FCC Class A, cTUVUS, CCC, EAC, KCC, RCM, BIS, BSMI
Garantie	Limited 3 years parts and labor
*Opmerking	* Only available on 220V input power and with lifetime of 16.500hrs @25°C/77°F

Laatst bijgewerkt: 09 Jul 2026

© 2026 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.