

ClickShare Hub Pro + Huddly® L1™ + Shure room system

Microsoft Teams Room bundle for enhanced collaboration in medium-to-large-sized meeting rooms.

- **Wireless presentation:** 4K content sharing with 2 next-gen ClickShare Buttons with USB-C DisplayPort™
- **Wireless BYOD for Microsoft Teams Rooms to run other videoconferencing platforms (Zoom, WebEx, Google Meet, etc.)**
- **Built on the Microsoft Device Ecosystem platform (MDEP)**
- **Dual display support**
- **Huddly® L1™ 6K camera with built-in AI director for visually engaging meetings**
- **Shure MXA902 ceiling**

The ClickShare Hub Pro, Huddly, and Shure bundle is a Microsoft Teams Rooms solution for medium-to-large meeting rooms. ClickShare Hub Pro enables effortless one-click wireless conferencing and 4K content sharing with two next-gen ClickShare Buttons (featuring Wi-Fi 6E and USB-C DisplayPort™) and dual-screen support.

The Huddly® L1™ delivers engaging video collaboration with an on-device AI director and exceptional image quality. The Shure MXA902 ceiling array microphone and loudspeaker with the ANIUSB-MATRIX USB audio network interface provide top-quality audio.

Технические характеристики**CLICKSHARE HUB PRO + HUDDL® L1™ + SHURE ROOM SYSTEM****Общие технические характеристики**

Операционная система	Android (MDEP)
Microsoft Teams Rooms license required	Yes
Системные требования	For ClickShare App. Minimum: Intel Core i3 or AMD Ryzen 5, 8GB RAM, Windows 10 20H2; Intel Core i3 or Apple Silicon M1, 8GB RAM, macOS 11 Big Sur Recommended: Intel Core i5/Ultra 5 or AMD Ryzen 7, 8GB RAM, Windows 11 latest build; Apple Silicon M3, 8GB RAM, macOS latest build
Видеовыходы	HDMI-1: UW5K WUHD (5120*2160) @30Hz HDMI 2.0 HDMI-2: 4K UHD (3840*2160) @30Hz HDMI 2.0 eDP (Control Panel): HD (1280*800) @60Hz DP 1.4
Видеовходы	4K UHD (3840*2160) @30Hz HDMI 2.0
Камера	Huddly® L1™ 6K conference camera with next-generation AI functionality, including industry-leading smart framing and advanced room analytics
Аудиовыход	USB-A 2.0/3.0 USB-C 2.0/3.0 HDMI 2.0
Устройства ClickShare Button	2 ClickShare Buttons 5th Generation
Микрофоны	MXA902 Ceiling Array Microphone + Loudspeaker: Single Zone Automatic Coverage™ technology to capture audio from a 20 by 20 foot (6 by 6 meter) area out of the box and integrated 2.5-inch wide-dispersion loudspeaker for clear, intelligible speech reproduction ANIUSB-MATRIX USB Audio Network Interface with Matrix Mixing: Connects 4 Dante audio inputs and 1 analog input to an A / V conferencing system or a PC-based videoconferencing application
Приложение ClickShare	Desktop
Уровень шума	Maximum 25 dBA @ 30°C
Протокол беспроводной передачи данных	IEEE 802.11 a/b/g/n/ac/ax/be and IEEE 802.15.1 BT 5.3
Охват	Max. 30m (100ft) between ClickShare Button and ClickShare Base Unit
Полоса частот	2.4GHz, 5GHz and 6GHz DBS/HBS (DFS channels supported in select number of countries)
Соединения	Back: 1x Ethernet LAN 1Gbit 1x USB-C Power delivery 3.1 EPR (for power adapter) 2x HDMI 2.0 output 2x USB-C 2.0/3.0 1x USB-A 2.0/3.0 1x USB-C 2.0/3.0 Device + USB-C DisplayPort™ output 1x USB-C 2.0 + USB-C DisplayPort™ output Front: 1x USB-C 2.0/3.0
Диапазон температур	Operating: 0°C + 40°C (+32°F to +104°F) Max 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to + 140°F)
Влажность	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Противоугонная система	Kensington lock
Сертификаты	FCC/CE
Подключение к сети	LAN
Управление и отчетность	Yes, XMS Cloud
Гарантия	3 years
Размеры (ВхШхГ)	37 * 180 * 180 (mm)
Потребляемая мощность	Operational: 160W (max) Standby:
Электропитание	External USB-C charger 100W (PD3.0 SPR), 180W (PD3.1 EPR)
Вес	720gr
ClickShare 10M 20W USB-C AOC Cable (Directional)	
Cable Length / Diameter	A0M / 6mm
Interface	USB Type-C 3.2 Gen1, DP 1.4
Power Delivery	20W

Технические характеристики**CLICKSHARE HUB PRO + HUDDL^Y® L1™ + SHURE ROOM SYSTEM**

Bend Radius	60mm/30mm (Fixed/Temporarily) While a minimum bend of 30mm is acceptable during handling or routing, it must not be maintained as a permanent fixture
Temperature range	Operating: -10°C + 60°C (+14°F to +140°F) Storage: -20°C to +70°C (-4°F to + 158°F)
Humidity	Storage/Operation: 0 to 85% relative humidity, non-condensing
Flame rated	VW-1 (Not plenum rated)
Power supply	
AC Input	100-240V~50-60Hz 1.4A
DC Output	100W max (20V 5A) / 45W (15V 3A) / 36W (12V 3A) / 27W (9V 3A) / 15W (5V 3A)
Output Plug	USB Type-C
Input AC Type	IEC60320-C6
Energy Efficiency Level	Comply with DOE standard Level VI
Altitude	5,000 meters
DC cable length	1.5m
Power cord	
Color	Black
Length	0.5m
Plug Type	EU / US / UK / CN / CH / IN / ZA / ANZ
Connector Type	IEC60320-C5
Control Panel	
Touchscreen	10.1-inch projected capacitive touchscreen with anti-fingerprint and anti-glare coatings, supporting up to 4 touch points for enhanced visibility and durability
Resolution	1280*800 @60Hz
Brightness	300 nits
Contrast ratio	1000:1
Viewing angle	80° (Up/Down/Left/Right)
Human detection sensor	Automatically detects in-room human movement within a 2-meter range and 90° field of view to wake the system.
Connections	USB Type-C 2.0, DisplayPort Alt Mode, PD3.0 Recommend using the included ClickShare 10M USB-C AOC cable for optimal performance
Anti-theft system	Kensington lock
Temperature range	Operating: 0°C + 40°C (+32°F to +104°F) Storage: -20°C to +60°C (-4°F to + 140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Dimensions (HxWxD)	254.5 x 187.9 x 76.9 (mm)
Power consumption	Powered over USB from connected Base Unit Operational: 7.3W (max) Standby:

Создано: 15 Jun 2026

© 2026 Барко нв. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Все названия брендов и продуктов являются товарными знаками, зарегистрированными товарными знаками или торговыми наименованиями соответствующих владельцев. В связи с непрерывными обновлениями информация и технические характеристики могут меняться без предварительного уведомления. Пожалуйста, проверьте www.barco.com для получения последних спецификаций.

www.barco.com

BARCO