

# ClickShare USB-C Extension over CAT kit



- Extends USB 2.0 and DisplayPort™ connectivity up to 40m with a standard CAT 5e (or higher)
- Enables 4K content sharing
- Connects the ClickShare Hub Base Unit with the Control Panel or user device
- Powered by the Base Unit, no extra power supply required
- Supports laptop charging with an additional power supply

The ClickShare CAT Extender over CAT kit makes complex meeting room installations easy by extending USB 2.0 and DisplayPort™ connectivity to 40m from the ClickShare Control Panel or meeting participant device. It supports intricate cable routing without signal loss and is powered by the ClickShare Hub—no extra power supply required. For meeting participants, it enables 4K content sharing with a wired connection and ensures uninterrupted collaboration thanks to its laptop-charging capabilities when connected to a power supply.

Expected to be available Jul 2026.

## Технические характеристики

## CLICKSHARE USB-C EXTENSION OVER CAT KIT

### Общие технические характеристики

|                              |   |
|------------------------------|---|
| <b>Системные требования</b>  | When connected with laptop for wired content sharing: USB 2.0/3.0, USB-C DP alt mode and PD charging  |
| <b>Resolution</b>            | When connects etween ClickShare Hub & Control Panel: -Cat 5e/Cat 6/Cat 6a/Cat 7: up to 1080p, 60Hz Between ClickShare Hub & Laptop for wired content sharing: -Cat 5e/Cat 6/Cat 6a/Cat 7: up to 4k, 30Hz  |
| <b>Соединения</b>            | TX box: USB-C Port-1: support DP signal(maximum 4k@30) and USB2.0 interface RJ45: for HDBaseT transmission, no ethernet connectivity USB-C Port-2: for external USB-C power adapter RX box: USB-C: support DP signal(maximum 4k@30) and USB2.0 interface RJ45: for HDBaseT transmission, no ethernet connectivity                                 |
| <b>Диапазон температур</b>   | Operational: 0°-40° Storage: -40°-85°   |
| <b>Влажность</b>             | Operational: 85% non-condensing Storage: 95% non-condensing   |
| <b>Гарантия</b>              | 1 year  |
| <b>Размеры (ВхШхГ)</b>       | 122 *152 *34 (mm)   |
| <b>Потребляемая мощность</b> | Between ClickShare Hub & Control Panel: TX box: 19.894W / RX box: 4.623W Between ClickShare Hub & Laptop for wired content sharing: TX box: 4.621W / RX box: 5.615W   |
| <b>Вес</b>                   | TX box: 333g RX box: 315g   |
| <b>Box content</b>           | TX box, RX Box, 1.2M USB-C to USB-C cable*2, screws   |
| <b>Resolution</b>            | When connects etween ClickShare Hub & Control Panel: -Cat 5e/Cat 6/Cat 6a/Cat 7: up to 1080p, 60Hz Between ClickShare Hub & Laptop for wired content sharing: -Cat 5e/Cat 6/Cat 6a/Cat 7: up to 4k, 30Hz  |
| <b>Maximum cable length</b>  | Between ClickShare Hub & Control Panel: -Cat 5e/Cat 6: up to 60m -Cat 6a/Cat 7: up to 70m Between ClickShare Hub & Laptop for wired content sharing: -Cat 5e/Cat 6: up to 35m -Cat 6a/Cat 7: up to 40m  |
| <b>Power</b>                 | Connected to ClickShare Hub & Control Panel: TX and RX power from ClickShare Hub Core/Pro Connected to ClickShare Hub & laptop: TX power from laptop, RX power from ClickShare Hub Core/Pro Connected to ClickShare Hub & laptop, with an external PSU: TX power from external USB-C power adapter (>100W), RX power from ClickShare Hub Core/Pro |
| <b>Compatibility</b>         | For connection between Base Unit and Control Panel: ClickShare Hub Core/Pro For wired content sharing: ClickShare Hub Core/Pro, ClickShare CX-50 Gen2, ClickShare Bar Pro   |
| <b>Mounting</b>              | Mounting holes build-in the housing for desk, ceiling or wall.  |

Создано: 01 Jun 2026

© 2026 Барко нв. Все права защищены. Полное или частичное воспроизведение без письменного разрешения запрещено. Все названия брендов и продуктов являются товарными знаками, зарегистрированными товарными знаками или торговыми наименованиями соответствующих владельцев. В связи с непрерывными обновлениями информация и технические характеристики могут меняться без предварительного уведомления. Пожалуйста, проверьте [www.barco.com](http://www.barco.com) для получения последних спецификаций.

[www.barco.com](http://www.barco.com)

