

ClickShare Hub Pro

Premium modular video conferencing room system for enhanced hybrid meetings in Microsoft Teams Rooms



- **Wireless presentation: 4K content sharing with 2 next-gen ClickShare Buttons with USB-C DisplayPort™**
- **Wireless BYOD for Microsoft Teams Rooms to run other videoconferencing platforms (Zoom, WebEx, Google Meet, etc.)**
- **Dual display support**
- **Secure by design, cloud-managed, and built on the Microsoft Device Ecosystem platform (MDEP)**
- **Sustainable product with Barco Eco label A+**
- **Works as part of a room system bundle certified for**

ClickShare Hub Pro is a premium, modular wireless video conferencing system for enhanced hybrid meetings.

The Hub Pro works with the ClickShare Control Panel* and enables participants to start their meeting with a simple tap. Sharing 4K content is just as easy with two next-gen ClickShare Buttons. Paired with dual display support, the Hub enhances engagement and collaboration.

For IT managers and integrators, ClickShare Hub Pro offers a customizable solution for all room types. Built on the Microsoft Device Ecosystem Platform (MDEP), it guarantees enterprise-grade security and compliance.

*The Control Panel, power cable and power cord are not included in this current package.

Product specifications

CLICKSHARE HUB PRO

General Specifications

Operating system	Android (MDEP)
Microsoft Teams Rooms license required	Yes
System requirements	For ClickShare App Minimum: Intel Core i3 or AMD Ryzen 5, 8GB RAM, Windows 10 20H2; Intel Core i3 or Apple Silicon M1, 8GB RAM, macOS 11 Big Sur Recommended: Intel Core i5/Ultra 5 or AMD Ryzen 7, 8GB RAM, Windows 11 latest build; Apple Silicon M3, 8GB RAM, macOS latest build
Video outputs	HDMI-1: UW5K WUHD (5120*2160) @30Hz HDMI 2.0 HDMI-2: 4K UHD (3840*2160) @30Hz HDMI 2.0 eDP (Control Panel): HD (1280*800) @60Hz DP 1.4
Video inputs	4K UHD (3840*2160) @30Hz HDMI 2.0
Audio output	USB-A 2.0/3.0 USB-C 2.0/3.0 HDMI 2.0
ClickShare Buttons	2 * ClickShare Button 5th Generation
ClickShare App	Desktop
Maximum sources simultaneously on screen	1
Noise Level	Maximum 25 dBA @ 30°C
Wireless transmission protocol	IEEE 802.11 a/b/g/n/ac/ax/be and IEEE 802.15.1 BT 5.3
Reach	Max. 30m (100ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4GHz, 5GHz and 6GHz DBS/HBS (DFS channels supported in select number of countries)
Connections	Back: 1x Ethernet LAN 1Gbit 1x USB-C Power delivery 3.1 EPR (for power adapter) 2x HDMI 2.0 output 2x USB-C 2.0/3.0 1x USB-A 2.0/3.0 1x USB-C 2.0/3.0 Device + USB-C DisplayPort™II output 1x USB-C 2.0 + USB-C DisplayPort™II output Front: 1x USB-C 2.0/3.0
Temperature range	Operating: 0°C + 40°C (+32°F to +104°F) Max 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to + 140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Network connection	LAN
Management and reporting	Yes, XMS Cloud
Warranty	3 years standard
Dimensions (HxWxD)	37 * 180 * 180 (mm)
Power consumption	Operational: 160W (max) Standby:
Power supply	External USB-C charger 100W (PD3.0 SPR), 180W (PD3.1 EPR)
Weight	720gr
Box content	ClickShare Hub Pro Base Unit, 2 ClickShare Hub Button 5th Gen, Mounting disc, Safety manual, Quick setup guide

Last updated: 11 Jun 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.