


Input module H 2.1, HDBaseT 3.0, SDI-12G, DMX, XLR - RMT

HDMI™ 2.1, 4x12G SDI, DMX, RMT XLR, HDBaseT 3.0



- Quad DP 1.2 input card
- DP 1.2 up to 4k60hz per connector
- Quad mode up to 4K240 (depending on the projector)
- Single , dual or quad DP 1.2 input compatibility

Product specifications**INPUT MODULE H 2.1, HDBASET 3.0, SDI-12G, DMX, XLR - RMT****General Specifications**

Dimensions (W x H x D)	30.0 x 14.0 x 40.0 cm
Weight	0.79 kg net -0.99 kg gross

Last updated: 28 Aug 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.