

ClickShare CX-20

Wireless conferencing system for small meeting rooms and huddle spaces



- **Entry-level wireless conferencing model**
- **Run video meetings from your laptop**
- **Iconic ClickShare Button for employees and guests**
- **Secure and cloud-managed**

ClickShare CX-20 enables wireless conferencing in small meeting spaces. When you walk into the meeting room, ClickShare automatically connects you to room devices like cameras, mics, speakers, sound bars and displays.

Start a meeting from your laptop within seconds, using your preferred video conferencing platform. Make hybrid meetings easy, with just one click on the ClickShare Button or the ClickShare App, both for employees and guests.

This product is certified with the Barco Eco label, reflecting its commitment to sustainability and environmental responsibility.

Product specifications**CLICKSHARE CX-20****General specifications**

Operating system	Windows 10 and higher macOS 11 (BigSur) and higher Android v11 and higher (ClickShare App) iOS 14 and higher (ClickShare App) update 37
System requirements	For a smooth experience with Microsoft Teams or Zoom Minimum: Intel i3 dual-core processor / 8GB RAM / OS: Windows 10 latest build or Mojave latest build Recommended: Intel i5 4-core processor / 8GB RAM / OS: Windows 10 latest build or Mac OS latest build qsd
Audio output	USB, HDMI qsd
USB	1 X USB-A, 1 X USB-C
ClickShare Buttons	1
Operating system for ClickShare button	test add
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast
	demo change
Maximum number of simultaneous connections (with Buttons and/or App)	32
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Wireless Frequency Band	test add
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHz and 5 GHz (DFS)
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbit 1x USB-C 2.0 (front); 1x USB-A 2.0 (front) -only Gen2: 1x USB-C 3.0 (front); 1x USB-A 3.0 (front)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock HELLO TEAM 5 :)
Certifications	FCC/CE
Touch screen support & Interactivity	/
Wireless conferencing	via App or Button
Local view	Local view of the room display only
Network connection	LAN & WiFi
Management and reporting	Yes
Warranty	1 year standard, 5 years coverage via SmartCare
*	test add
ClickShare Base Unit dimensions	
Dimensions (HxWxD)	34 mm x 135 mm x 135 mm
Power supply	Standard 110/220 V AC plug or USB-C (only Gen2)
Power consumption	Operational: 5-10W, 24W Max
Weight	900 gr
Dimensions (HxWxD)	test add
Power consumption	test changee
Weight	test add
Test category jordy	
Test field jordy	test value for test category

Last updated: 09 Oct 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.