

# ClickShare Hub Pro + Huddly<sup>®</sup> L1<sup>™</sup> + Shure room system

Microsoft Teams Room bundle for enhanced collaboration in medium-to-large-sized meeting rooms.

- **Wireless presentation: 4K content sharing with 2 next-gen ClickShare Buttons with USB-C DisplayPort<sup>™</sup>**

The ClickShare Hub Pro, Huddly, and Shure bundle is a Microsoft Teams Rooms solution for medium-to-large meeting rooms.

ClickShare Hub Pro enables effortless one-click wireless conferencing and 4K content sharing with two next-gen ClickShare Buttons (featuring Wi-Fi 6E and USB-C DisplayPort<sup>™</sup>) and dual-screen support.

- **Wireless BYOD for Microsoft Teams Rooms to run on other videoconferencing platforms (Zoom, WebEx, Google Meet, etc.)**

The Huddly<sup>®</sup> L1<sup>™</sup> delivers engaging video collaboration with an on-device AI director and exceptional image quality. The Shure MXA902 ceiling array microphone and loudspeaker with the ANIUSB-MATRIX USB audio network interface provide top-quality audio.

- **Built on the Microsoft Device Ecosystem platform (MDEP)**
- **Dual display support**
- **Huddly<sup>®</sup> L1<sup>™</sup> 6K camera with built-in AI director for visually engaging meetings**
- **Shure MXA902 ceiling ar**

**技術仕様****CLICKSHARE HUB PRO + HUDDL<sup>®</sup> L1™ + SHURE ROOM SYSTEM****一般仕様**

オペレーティングシステム	Android (MDEP)
Microsoft Teams Rooms license required	Yes
システム要件	For ClickShare App. Minimum: Intel Core i3 or AMD Ryzen 5, 8GB RAM, Windows 10 20H2; Intel Core i3 or Apple Silicon M1, 8GB RAM, macOS 11 Big Sur Recommended: Intel Core i5/Ultra 5 or AMD Ryzen 7, 8GB RAM, Windows 11 latest build; Apple Silicon M3, 8GB RAM, macOS latest build
ビデオ出力	HDMI-1: UW5K WUHD (5120*2160) @30Hz HDMI 2.0 HDMI-2: 4K UHD (3840*2160) @30Hz HDMI 2.0 eDP (Control Panel): HD (1280*800) @60Hz DP 1.4
ビデオ入力	4K UHD (3840*2160) @30Hz HDMI 2.0
カメラ	Huddly <sup>®</sup> L1™ 6K conference camera with next-generation AI functionality, including industry-leading smart framing and advanced room analytics
オーディオ出力	USB-A 2.0/3.0 USB-C 2.0/3.0 HDMI 2.0
ClickShareボタン	2 ClickShare Buttons 5th Generation
マイク	MXA902 Ceiling Array Microphone + Loudspeaker: Single Zone Automatic Coverage™ technology to capture audio from a 20 by 20 foot (6 by 6 meter) area out of the box and integrated 2.5-inch wide-dispersion loudspeaker for clear, intelligible speech reproduction ANIUSB-MATRIX USB Audio Network Interface with Matrix Mixing: Connects 4 Dante audio inputs and 1 analog input to an A/V conferencing system or a PC-based videoconferencing application
ClickShare アプリ	Desktop
ノイズレベル	Maximum 25 dBA @ 30°C
無線伝送プロトコル	IEEE 802.11 a/b/g/n/ac/ax/be and IEEE 802.15.1 BT 5.3
Reach	Max. 30m (100ft) between ClickShare Button and ClickShare Base Unit
周波数帯域	2.4GHz, 5GHz and 6GHz DBS/HBS (DFS channels supported in select number of countries)
接続	Back: 1x Ethernet LAN 1Gbit 1x USB-C Power delivery 3.1 EPR (for power adapter) 2x HDMI 2.0 output 2x USB-C 2.0/3.0 1x USB-A 2.0/3.0 1x USB-C 2.0/3.0 Device + USB-C DisplayPort™ output 1x USB-C 2.0 + USB-C DisplayPort™ output Front: 1x USB-C 2.0/3.0
温度範囲	Operating: 0°C + 40°C (+32°F to +104°F) Max 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
湿度	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
盗難防止システム	Kensington lock
証明書	FCC/CE
ネットワーク接続	LAN
管理と報告	Yes, XMS Cloud
保証	3 years
寸法 (高さx幅x奥行き)	37 * 180 * 180 (mm)
消費電力	Operational: 160W (max) Standby:
電源	External USB-C charger 100W (PD3.0 SPR), 180W (PD3.1 EPR)
重量	720gr
<b>ClickShare 10M 20W USB-C AOC Cable (Directional)</b>	
Cable Length / Diameter	A0M / 6mm
Interface	USB Type-C 3.2 Gen1, DP 1.4

**技術仕様****CLICKSHARE HUB PRO + HUDDL<sup>Y</sup>® L1™ + SHURE ROOM SYSTEM**

Power Delivery	20W
Bend Radius	60mm/30mm (Fixed/Temporarily) While a minimum bend of 30mm is acceptable during handling or routing, it must not be maintained as a permanent fixture
Temperature range	Operating: -10°C + 60°C (+14°F to +140°F) Storage: -20°C to +70°C (-4°F to + 158°F)
Humidity	Storage/Operation: 0 to 85% relative humidity, non-condensing
Flame rated	VW-1 (Not plenum rated)
<b>Power supply</b>	
AC Input	100-240V~50-60Hz 1.4A
DC Output	100W max (20V 5A) / 45W (15V 3A) / 36W (12V 3A) / 27W (9V 3A) / 15W (5V 3A)
Output Plug	USB Type-C
Input AC Type	IEC60320-C6
Energy Efficiency Level	Comply with DOE standard Level VI
Altitude	5,000 meters
DC cable length	1.5m
<b>Power cord</b>	
Color	Black
Length	0.5m
Plug Type	EU / US / UK / CN / CH / IN / ZA / ANZ
Connector Type	IEC60320-C5
<b>Control Panel</b>	
Touchscreen	10.1-inch projected capacitive touchscreen with anti-fingerprint and anti-glare coatings, supporting up to 4 touch points for enhanced visibility and durability
Resolution	1280*800 @60Hz
Brightness	300 nits
Contrast ratio	1000:1
Viewing angle	80° (Up/Down/Left/Right)
Human detection sensor	Automatically detects in-room human movement within a 2-meter range and 90° field of view to wake the system.
Connections	USB Type-C 2.0, DisplayPort Alt Mode, PD3.0 Recommend using the included ClickShare 10M USB-C AOC cable for optimal performance
Anti-theft system	Kensington lock
Temperature range	Operating: 0°C + 40°C (+32°F to +104°F) Storage: -20°C to +60°C (-4°F to + 140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Dimensions (HxWxD)	254.5 x 187.9 x 76.9 (mm)
Power consumption	Powered over USB from connected Base Unit Operational: 7.3W (max) Standby:

**生成日:15 Jun 2026**

© 2026 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。