

Residential - Vali NT1.5-I

1.5 mm Pixel Pitch, High-Resolution DV-LED Display



- **Stunning picture quality with less power consumption** With no visual distortion, low latency and perfect syncing; NT Vali 1.5 brings movies, sports and TV programming to life. This also requires perfect color accuracy at every level of brightness, which is maintained by Infinipix® Gen2. Proprietary Smart Calibration™ also ensures wide color gamut support for rich and true-to-life images.
- **Designed for any space** The thin tiles contribute to versatility and ease of installation. This lowers the wall's footprint and broadens the possibilities for set-

Vali is the son of Odin, the most powerful god in Northern mythology. The latest addition to our Northern Lights series, our Barco Residential NT Vali 1.5 DV-LED wall has the power to conquer the sunniest room, and the finesse to bring movie magic to a dedicated private theater.

Our 1.5mm pixel pitch direct view LED can be configured in a wide range of sizes and shapes. Imagine a screen that never has to turn off. When you're not watching movies or your favorite sports, it is a perfect canvas for digital art. Images are razor sharp, and Barco uses state-of-the-art Infinipix processing to for impressive color fidelity.

Barco Residential White Glove Service is included. Factory trained Barco engineers take care of the installation to insure an exceptional result.

技術仕様

RESIDENTIAL - VALI NT1.5-I

LEDタイトル	
ピクセルピッチ	1.56 mm
モジュールあたりのピクセル	384x216 (水平x垂直)
寸法	(幅x高さx奥行き) 600x337.5x39mm / 23.62"x13.29"x1.54"
重量	6kg/タイル
LED寿命	100,000時間 (ビデオ -50%輝度)
輝度	>1000 nit
ピーク輝度	780ニット
内部処理	23ビット
色深度	16ビット (281兆色)
シェーダー	なし
Control	インフィンピックス™ Gen2
リフレッシュレート@60Hz	3,840 Hz
3D	なし
フレームレート	24 / 25 / 29.97 / 30 / 47.95 / 48 / 50 / 59.94 / 60
水平視野角	160° +/-5°
垂直視野角	160° +/-5°
明るさの均一性	>98%
調光	0-100%
コントラスト	7,500:1 (at 10 lux)
消費電力	544 W/m ² 110 W/タイル (最大) 151 W/m ² 31 W/タイル (標準)
熱放散	1,856 BTU/h/m ² (最大) 515 BTU/h/m ² (通常)
放熱 (前面/背面)	54%/46%
動作電源電圧	AC電源: 100-240V 50/60Hz
動作湿度	10 -80%
動作温度	-10°C~+40°C / 14°F~104°F
冗長性	電源: オプション データ: 信号ループ冗長性/N+N冗長性はオプション
HDR	HLG/HDR10対応
凹曲面	タイル間最大5° (半径6.88m)
凸曲面	N/A
保守性	フルフロント & フルバックサービス
ケーブル管理	外部ケーブルなし
人間工学	目の疲れを軽減するSteadyView™ドライバーアルゴリズム
証明書	CE、UL、FCCクラスA、CB、RoHS、WEEE、REACH
TAA準拠	利用不可
保証	3年
EssentialCareサービスの提供	5年

生成日:21 May 2026

© 2026 Barco nv.(C) Barco. All rights reserved. (無断転載を禁ず。) 書面による許可なく全部または一部を複製することは禁止されています。すべてのブランド名および製品名は、それぞれの所有者の商標、登録商標、または商号です。継続的な技術革新により、情報および技術仕様は予告なく変更される場合があります。最新の仕様についてはwww.barco.comをご確認ください。