

F400-4K

4K UHD up to 120Hz projector



- **Up to 4K resolution @60-120Hz framerate for great image performance**
- **Revolutionary static laser-phosphor for speckle-free, outstanding image quality**
- **Rock-solid and true solid-state, fully rated for shock and vibration**
- **Next Gen Barco Pulse for more powerful processing and unified interface across all Barco projectors**
- **5 years warranty as standard**
- **Also available: FS400-4K with dedicated IR for NVG training**

The F400-4K is a true solid-state static laser-phosphor projector designed for the simulation and training market. With a resolution up to 4K, the F400-4K is built for the most challenging environments. The F400-4K was designed specifically for the demands of the training and simulation customer, and breathes the needed sense of realism into every simulation system.

With its processing speeds of up to 120 Hz (at WQXGA resolution), the F400-4K brings all details to life in the most dynamic, high-speed environments. This great performance never comes at a cost of the image quality, which follows the scenario perfectly, at lowest latency.

Designed to perform - in all circumstances

The F400-4K also benefits from the next generation proprietary Barco Pulse electronics - the powerful and flexible software architecture that ensures advanced low-latency processing operations, like pixel-shifting, warping and blending, to take place in one single processing step. This is a huge advantage in the real-time processing environment of most simulator systems today. What's more, our API enables partners to integrate custom management tools and value-add features to complement the projector's software.

Motion platforms, with their rapid sudden movements, are



challenging environments for projectors. The F400-4K is a true solid-state product, which means no moving parts like color or phosphor wheels and is fully rated for shock and vibration. With the electronics, hardware and software built around a unique H-beam shaped aluminum core, the F400-4K has an optimized strength-to-weight ratio providing a sturdy platform as well as easy access if servicing is required. Optional accessories to support the lens on motion-based platforms are also available, contributing to even higher image robustness.

A dedicated FS400 series, designed for NVG stimulation applications, features a powerful IR light source with increased intensity.

Product specificaties**F400-4K****Algemene specificaties**

Helderheid	5,400 typical ANSI lumens 5,750 typical center lumens
Contrastverhouding	1,800 – 6,000:1 sequential
IR voor NVG	No
Uniformiteit van de helderheid	90%
Aspectverhouding	16:10
Type projector	1-chip DLP laser phosphor
Resolutie	2,560 x 1,600 (WOXGA native) 3,840 x 2,400 (4K UHD)
Type lens	FLD+ / FLDX
Optische lensverschuiving	Vertical up to 144% depending on iris Horizontal up to 71% depending on lens Motorized zoom & Focus + Lens memory (FLDX) Motorized lens shift (all lenses)
Kleurcorrectie	P7 RealColor™
Kleurruimte	REC709
CLO (constante lichtopbrengst)	Yes
Lichtbron	Static laser phosphor
Levensduur lichtbron	Minimum 25,000 hours @ full power Up to 50,000 hours, depending on mode of operation
Verzegelde DLP™ core	Yes
Oriëntatie	360° rotation no restrictions
3D	Active stereoscopic 3D
Beeldverwerking	Embedded warp & blend
Keystone-correctie	Yes
Ingangen	1 x DP 1.4 (HDCP 2.2) 1 x HDMI™ 2.1 (HDCP 2.2) 4 x DP 1.2
Invoerresolutie	Including and up to: 3840 x 2400 @ 60Hz 3840 x 2160 @ 60Hz 4096 x 2160 @ 60Hz 2560 x 1600 @ 120Hz
Kleurdiepte invoeren	Up to 12-bit, depending on configuration
Softwaretools	Pulse Toolset + Android app + iOS app
Bediening	IR, RJ45, Cabled Remote Control
Netwerkverbinding	10/100/1000 Mbit
Stroomvereisten	100-240V / 50-60Hz
Stroomverbruik	815W typical 1200W maximum rated
BTU per uur	2781 BTU/h typical 4095 BTU/h maximum
Geluidsniveau (typisch bij 25°C/77°F)	34 db(A)
Temperatuur tijdens gebruik	10°-40°C (sea level)
Stand-by vermogen	< 0.5W
Temperatuur bij opslag	-20 to 60 °C
24/7 werking	Yes
Luchtvochtigheid tijdens gebruik	20 -80% RH (no condense)
Luchtvochtigheid bij opslag	10 -90% RH (no condense)
Afmetingen (B x L x H)	472 x 562(542) x 293 mm / 18,6 x 22,1(21,3) x 11,5 in (front cover removed)
Gewicht	31Kg / 68Lbs (no lens)
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	CE, FCC Class A and cSGSUS, KCC, CCC
Garantie	Limited 5 years on parts and labor Extentable

Laatst bijgewerkt: 18 Jun 2026

© 2026 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.