


# RGB Laser ODL-821

80" laser-lit rear-projection video walls for 24/7 control rooms



- **1.5x more brightness than mainstream 80" LED-lit rear-projection video walls**
- **25% less power consumption at higher brightness levels**
- **More than 11 years of uninterrupted operation in 24/7 mode**
- **Unmatched colors, focus, and contrast levels**
- **Lower price/m<sup>2</sup> (compared to 70" cubes)**
- **Silent like never before ('library' noise level)**
- **Redundancy of critical components for ultimate**

Powered with the latest laser technology, Barco's RGB laser rear-projection video walls delivers unseen brightness levels and vibrant colors, while offering a very low total cost of ownership (TCO). With its 10th generation of rear-projection video walls, Barco again raises the bar for critical infrastructure visualization.

Providing 1.5x more brightness than mainstream 80" LED-lit rear-projection video walls, the RGB Laser series removes all brightness issues of earlier video walls. The high luminance allows operation under daylight conditions, so control rooms can finally light up -which improves operator working conditions! Adding vibrant colors to this mix (making all nuances clearly distinguishable), ensures that nothing is wrongly interpreted and situational awareness is enriched. What's more, using 80" cubes results in a lower price per square meter and less seams for the large video wall.

## Over 11 years of uninterrupted 24/7 operations

With the RGB laser for 24/7 control rooms series, Barco takes another giant leap forward in terms of reliability. With a light source lifetime of at least 125,000 hours in both normal and eco-mode, and redundancy of all critical components (including power supply, inputs, and laser drivers), nothing is left to chance when it comes to uptime. Unlike technology used by others and for non-24/7 environments, Barco's RGB laser display series doesn't need a rotating color wheel to operate. Since each color can be uniquely controlled and is not dependent on the segment of a color wheel, it provides color control like never before and eliminates color breakup.

## Automatic calibration and alignment

The engine of Barco's RGB laser for 24/7 control rooms is fully motorized. Installers and maintenance staff will never need to open up the individual

The engine of Barco's RGB laser for 24/7 control rooms is fully motorized. Installers and maintenance staff will never need to open up the individual modules to perfectly align the individual cubes of the video wall. Using a web interface, the video wall can be remotely aligned by a single technician - including keystone correction. Combined with the Sense X automatic calibration system, which continuously measures and adjusts brightness and color levels over the complete video wall, users are sure the complete canvas is perfectly balanced at any time.

**Product specifications****RGB LASER ODL-821****General specifications**

Resolution	Full HD (1920 x 1080 pixels)			
On-screen brightness (under native color gamut)	Mode	Brightness	Light source lifetime (hrs)	Power usage (W)
	Boost	500 cd/m <sup>2</sup>	60,000	260
	Normal	390 cd/m <sup>2</sup>	125,000	200
	Eco	195 cd/m <sup>2</sup>	125,000	120
On-screen contrast	1800:1			
Screen	BBP Horizontal half gain viewing angle: 30° Vertical half gain viewing angle: 30°			
Color	Up to 170% REC709 color triangle			
Display technology	Rear projection DLP (rear access only)			
White point	Customized white points			
Brightness uniformity	Typ. >95% ANSI 9			
	Typ. >90% ANSI 13			
Screen gap	Hor: 1.2 mm, Vert. 0.8 mm (@ 25°C)			
Color stability	Sense X automatic calibration			
Dimensions	<ul style="list-style-type: none"> <li>• Diagonal: 80" (Approx.)</li> <li>• Width: 1,760 mm   69.29"</li> <li>• Height: 990 mm   38.97"</li> <li>• Depth: 730 mm   28.74"</li> <li>• Weight: Projection Module: 65.5 Kg   144.4 lbs</li> <li>• Weight: Support frame (1m): 42 Kg   92.5 lbs</li> </ul>			
Light source	RGB lasers illumination (Lasers Class 1 RG2)			
Redundancy	Redundant laser banks with redundant power supply drivers, input signal & external power supply			
Light source lifetime	> 125,000 hrs in both Normal and Eco mode			
Noise Level	Less than 20 dB (measured from 3 meters in front)			
Conditions for operation	10°C-40°C   50°F-104°F			
	Up to 80% humidity (non-condensing)			
AC input voltage	100 – 240 VAC, 50-60Hz			
Power	120W (eco)			
	200W (normal)			
Heat dissipation	390 BTU/h (eco)			
	680 BTU/h (typ)			
	860 BTU/h (max)			
Connectivity	2x DP1.2 inputs & 1x output (4K@60Hz)			
	2x HDMI™ 2.0 inputs (4K@60Hz)			
	2x USB ports (only for power)			
	2x Ethernet ports			
Signal processing	Loop through			
	Cropping, scaling with wall configuration			
Direct ethernet access	Built in web server			
Graphical user interface	All settings and operational parameters			
Integration to third party equipment	WEB service API			
Warranty	2 years			

Last updated: 21 May 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.