

# TransForm NDN-220 Pro

Networked Display Node



Barco's TransForm N Networked Display Node is a powerful PC-based networked graphics processor. It is used in the networked visualization environment of a TransForm N system and can display encoded streams coming from the Gbit Ethernet/IP network. H-264, V2D and ProServer represent just the top of a long list of supported codecs and streaming formats. Furthermore, the display controller also has a high-end graphics card to perform the rendering operations as are requested by the TransForm N management clients in the network.

## High density content – Large display walls

The NDN-220 Pro Output nodes can display high density content and can drive up to sixteen HD displays with a single node. The unit supports multiple different types of displays including the whole range of Barco display solutions like RPC, LCD & LED. Managed by CMS inside the TransForm N system multiple NDN-220 Pro output nodes can be combined in a wall-cluster to show a composed synchronized picture on display walls of virtually unlimited size. The NDN-220 Pro offers a dedicated sync-cable based full frame-lock synchronization between up to 30 nodes suiting the needs of video-walls with advanced synchronization requirements.

## Features:

- 4 DisplayPort 1.2 outputs
- Up to 4K-UHD resolution per output
- Universal IP video streaming decoding
- Most extensive list of supported codecs and formats

- Network-based content synchronization between multiple display nodes driving a single wall
- Frame lock between multiple display nodes
- Redundant network interface
- Silent operation in a compact and flexible form factor
- Mature Barco quality, robust and reliable
- The NDN-220 Pro has a performance to show up to 12 full HD camera sources per node

**Product specifications****TRANSFORM NDN-220 PRO****General specifications**

Memory	8 GB
Disk drive	128 GB Solid-State Disk SSD
Network	2x 1Gb/s LAN
Graphics card	Professional high-performance NVIDIA Quadro-series graphic card
Processor	Intel(R) Core(TM) i5-9500E 6-core processor 3.0GHz (4.2GHz max. Turbo frequency)
Output	4x Display Port 1.2 (supporting up to 4x 4K-UHD) 4x DVI-SL via included adapters (supporting up to 4x HD)
Input	H.264, MPEG-2/4, V2D, H.263, VNC, Pro-Server (see supported codec list)
Form factor	3U ½ 19" Rackmount housing
Dimensions	131.5mm x 220mm x 305mm   5.18" x 8.66" x 12.01"
Weight	6.1 kg (7.9 kg incl. packaging)
Power supply	100-240V, 8-4A, 50/60Hz
Power consumption	270 W (max)
Temperature range	0° -40°C   32° -104°F
Humidity	Max. 80% (noncondensing)
Altitude	Up to 5000m (operation)
Noise Level	Max. 35dbA (measured at 1m/32.8ft distance at 22°/72)
Compliance	CE, UKCA, CB/UL 60950/62368-1, ICES, CCC, FCC Class A Regulatory Model Id: P220
Order Information	R9822000   NDN-220 PRO Display Node (no power cable) R9822000B   NDN-220 PRO Display Node (US) R9822000D   NDN-220 PRO Display Node (IN) R9822000F   NDN-220 PRO Display Node (EU) R9822000G   NDN-220 PRO Display Node (UK) R9822000I   NDN-220 PRO Display Node (CN) R9822000X   NDN-220 PRO Display Node (C13/C14 power cable) R9821099   Rackmount kit for 2x NDN-220 PRO/LITE R766042   Pedestal mount kit for NDN-220 PRO/LITE

**Last updated: 21 May 2026**

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.