


FLDX 0.8 : 1 (EN62) lens

Wide-angle fixed lens for F40/F70/F90/F400



This is a new, high-resolution all-glass lens replacing the EN42 and NV42. It comes with motorized and index-based iris and focus to accommodate for an accurate set/get value. It is also optimized for night vision and IR transmission for training using NVGs.

Can also be used on the Barco F80-series with adapter and specific software.

If used with the F400-N4K, please contact your Barco representative.

Product specifications**FLDX 0.8 : 1 (EN62) LENS****General Specifications**

Lens type	Wide angle lens (On-axis) for F40/F70/F90 projector series – with indexing encoders
Throw Ratio	DMD chip ■ WQXGA 0.8:1 ■ 1080p /WUXGA 0.75:1 ■ SXGA+ 0.81:1 ■ F80 1.06:1 ■ F400-N4K 0.70:1 (Requires the use of individual F400-lens adapters) ■ Image size tolerance +/- 2%
Working F/#	F 2.1 Motorized Iris F# 2.1-6.5
Focal length	16.12 mm
Focus Range	Optical Performance : 0.7m –7m Mechanical (0.5-10m)
Weight	2.7 kg

Last updated: 01 Sep 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.