


MNA-420 ENC ANA

HD AV-to-IP adapter for the OR and interventional suite



- AV-to-IP conversion
- Secure, scalable and flexible solution
- Established 3rd generation technology
- Near-zero latency for real-time decision making

The MNA-420 ENC ANA converts VGA & CVBS or VGA & S-Video video signals to Nexxis RAW IP packets. Other non-video signals such as audio and USB for keyboard/mouse are also supported. End-to-end video latency is amazingly low and is guaranteed not to exceed a single frame.

Capabilities

The MNA-420 adapters are part of Barco's Nexxis 2 solution, which provides users with uncompromised networked visualization for digital operating, endoscopy, and interventional rooms. The compact Nexxis 2 AV-to-IP adapters offer simplicity and flexibility while maintaining the highest possible performance standards and fitness for use in demanding medical environments.

As a third-generation device, the MNA-420 ENC ANA provides the full richness of the established Nexxis platform while:

- increasing future scalability
- improving ease of installation
- adding increased security performance
- reducing ecological footprint

Nexxis 2 is not available for distribution in certain markets, including the United States, where FDA 510(k) clearance is pending. Please contact your Barco representative to confirm availability in your region.

Product specifications

MNA-420 ENC ANA

General Specifications

Video conversion	Converts analog video signals to uncompressed IP streams
Processing	One channel S-video/CVBS (720x576i50 or 720x485i60) + one channel analog graphical source (1920x1200p60 with reduced blanking)
Color depth	CVBS/S-Video: YCbCr 4:2:2 10 bit/color VGA: RGB24 8 bit/color & RGB30 10bit/color
Latency	Subframe
Security	AES 128 encryption of all video, data & control signals
Encoder system	N/A
Video Output	N/A
Video Input	1x DIN + 1x DSUB-15 + 2x BNC
Network output	1x PAL/NTSC uncompressed IP stream + 1x HD uncompressed IP stream
IP Connectivity	1x 10GbE Fiber Optic Interface with SFP+ module
IP Standards	IPv4, IGMP, DHCP, sRTP, sRTCP, 802.1q, AES 128b, HTTP(s)
USB	1x micro-USB type B & 1x USB Type A
USB Power Output	Max. 5 V / 500 mA (2.5 W) per USB 2.0 Type-A port
Audio	Stereo line in 15mm length compatible 3.5mm TRRS jack Microphone in 15mm length compatible 3.5mm TRRS jack Stereo line out/Headset 15mm length compatible 3.5mm TRRS jack
Compliance	N/A
GPIO	2x GPI + 1x GPO via 15mm length compatible 3.5mm TRRS jack Camera trigger is possible via stereo line in (1x), microphone in (1x) and GPIO (2x) connector
Nexxis Integration	Fully integrated in the NexxisOR 2.x solution, compatible with MNA-240 and MNA-4x0 devices
PSU	External 12Vdc Medical Approved PSU, 100-240VAC 50-60Hz 60W with lockable connector at DC side
Power Consumption	Maximum: 19,2 W Typical: 8,8 W
Size	35,8 mm H x 147,5 mm W x 167,4 mm D 1,4" H x 5,8" W x 6,6" D (+/-2 mm / 0.1")
Weight	MNA-420 ENC ANA unpacked has a weight equal to 540g
Temperature	5°C to 40°C (41°F to 104°F)
Humidity	Maximum 85%
Altitude	700 hPa
Storage conditions	Storage temperature: -20°C to 60°C (-4°F to 140°F) Storage relative humidity: 10% to 93% Storage altitude: 500 hPa
Acoustic noise level	Typical 20dBA at 20°C at 1m
Mounting	Versatile mounting bracket included
Certifications	-CB (IEC 60601-1) -CB (IEC 62368-1) -cRU, RU (cRUus) -Demko -CE medical device class I -UKCA -BIS Registration, IS 13252 (part 1)
Standards	Medical Equipment: -IEC 60601-1:2005 + A1:2012 + A2:2020 -IEC 60601-1-6:2010 + A1:2013 + A2:2020 -IEC 60601-1-2:2014+A1:2020 (Ed.4.1) -AAMI ES 60601-1:2005 + A1:2012 + A2:2021 -CAN/CSA-C22.2 No.60601-1-08 + A1:14 (Reaffirmed 2022) -EN 60601-1:2006 + A1:2013 + A12:2014 + A2:2021 + A13:2024 -EN 60601-1-6:2010 + A1:2015 + A2:2021 -EN 60601-1-2:2015+A1:2021 (Ed.4.1) -FCC class B -ICES-001 Level B ITE Equipment: -IEC 62368-1:2018 -EN IEC 62368-1:2020 + A11:2020 -IS 13252 (Part1): 2010
3D Video Support	N/A
Streamback	N/A

Last updated: 06 Aug 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.