

NGS-D440

Compact 4K60 Encoder



- **Superb image quality**
- **Network integrated**
- **Easy installation and configuration**
- **High performance**
- **Designed for 24/7 operation**
- **Part of the TFN and CTRL Product families**

Barco's NGS-D440 is a powerful encoder. This device enables the support of HDMI™ 2.0 compliant 4K60 AV sources.

Key features:

- **Superb image quality**The NGS-D440 comes with Barco's latest image processing engine, which provides the best scaling and color space conversion algorithms on the market today. Furthermore, resolutions up to 4K60 are supported through an industry-standard protocol.
- **Network IT-integrated**The NGS-D440 requires standard IT services (DHCP, DNS, NTP) to be available in the network during operation. This allows to easily change the network configuration without the need to reconfigure the system. Furthermore, it provides easy and central management through its configured host name in your domain (no need to remember IPs).
- **Easy installation & configuration**Because of the above-mentioned network integration, the device discovery is faster and simpler than ever. Additionally, it is very easy and fast to create a source via a utility button that can be used to identify a device.
- **Performance**The NGS-D440 comes with an HDMI™ 2.0 input. This input supports up to UHD (3840 x 2160) at 60fps and features an active loop-through that creates a 1:1 copy of the input. Furthermore, the power (PoE+ and USB-C) and the network (bonding) redundancy guarantee a high uptime of the device.

Product specifications

NGS-D440

General specifications

Resolutions and frame rates	For a full list of resolutions please check the Barco CTRL Features and Specifications document. 16:9 up to 3840 x 2160 60Hz 21:9 up to 2560 x 1080 @ 60fps up to 3440 x 1440 @ 60fps up to 3840 x 1600 @ 60fps 32:9 up to 3840 x 1080 @ 60fps
Video inputs	1 HDMI™ 2.0 input 1 HDMI™ 1.4 input
Video outputs	1 HDMI™ 2.0 output
Network connection	2 RJ45 (1Gb copper) – active failover
EMI / EMC	CE, UL, BIS, RCM, EAC, BSMI, TAA
USB	2 USB 2.0 Type C connectors
Platform	Applicable for use in Barco CTRL and Transform N systems
Heat dissipation	63,94 BTU/h/m ² (typ) / 85,48 BTU/h/m ² (max)
Dimensions (HxWxD)	136 mm x 136 mm x 30 mm 5.35" x 5.35" W x 1.18"
Weight	510g ± 50g (1.2 lbs)
Audio	Up to 2 audio channels (HDMI, Line In)
Power supply	20V 2.25A, (45W) external USB-C power supply or 25W on PoE+ (802.3at)
Power consumption	Typical power dissipation 18,7W -Maximum power dissipation 25W
Number of channels	2
Chroma subsampling	4:2:2
Bandwidth	Video: avg 60 Mbps for a 3840x2160 at 60Hz
Operating conditions	
Noise level	19dBA at 25°C
Environmental temperature	0°C to 40°C (32°F to 104°F)
Order Information	R9867440 Compact 4K60 Encoder

Last updated: 21 May 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.