

ClickShare Control Panel



- **One-tap start to your hybrid meeting — no delays, no confusion**
- **Included: single 10m USB-C connection ensures a clean setup**
- **Optional: CAT extender kit for flexible installation**
- **Zero setup time, easy deployment and management**
- **10-inch responsive screen with multiple mounting options**

The ClickShare Control Panel is an integral part of ClickShare Hub wireless video conferencing room system, providing an intuitive interface to start and manage hybrid meetings. With a single tap, you can launch your Microsoft Teams video call, ensuring a smooth and efficient meeting experience.

Product specifications

CLICKSHARE CONTROL PANEL

General specifications

Touchscreen	10.1-inch projected capacitive touchscreen with anti-fingerprint and anti-glare coatings, supporting up to 4 touch points for enhanced visibility and durability
Resolution	1280*800 @60Hz
Brightness	300 nits
Contrast Ratio	1000:1
Viewing angle	80° (Up/Down/Left/Right)
Human detection sensor	Automatically detects in-room human movement within a 2-meter range and 90° field of view to wake the system.
Connections	USB Type-C 2.0, DisplayPort Alt Mode, PD3.0 Recommend using the included ClickShare 10M USB-C AOC cable for optimal performance
Temperature range	Operating: 0°C + 40°C (+32°F to +104°F) Storage: -20°C to +60°C (-4°F to + 140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Dimensions (HxWxD)	254.5 x 187.9 x 76.9 (mm)
Power consumption	Powered over USB from connected Base Unit Operational: 7.3W (max) Standby:
Weight	820gr
Box content	ClickShare Control Panel, ClickShare 10M 20W USB-C AOC cable, L-Shape mounting plate, Round base, Screw pack, Safety manual, Quick setup guide

ClickShare 10M 20W USB-C AOC Cable (Directional)

Cable Length / Diameter	10M / 6mm
Interface	USB Type-C 3.2 Gen1, DP 1.4
Power Delivery	20W
Bend Radius	60mm/30mm (Fixed/Temporarily) While a minimum bend of 30mm is acceptable during handling or routing, it must not be maintained as a permanent fixture.
Temperature range	Operating: -10°C + 60°C (+14°F to +140°F) Storage: -20°C to +70°C (-4°F to + 158°F)
Humidity	Storage/Operation: 0 to 85% relative humidity, non-condensing
Flame rated	VW-1 (not plenum rated)
Box content	ClickShare 10M 20W USB-C AOC cable, USB-C cable lock kit

Last updated: 21 May 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.