

eGPU Solution

Flexible home-read solution for diagnostic work



- 1 x preinstalled Barco MXRV-3100 display controller
- 1 x Thunderbolt™ 5 upstream port with 96W power delivery
- 1 x Thunderbolt™ 5 downstream port with 15W power delivery
- 1 x USB 3.2 Gen2 Type-C
- 3 x USB 3.2 Gen2 Type-A
- 1 x 2.5 Gigabit Ethernet

Barco eGPU Solution transforms a compatible Thunderbolt-enabled Windows laptop into a high-performance workstation setup through a single-cable connection. In combination with the preinstalled Barco MXRV-3100 display controller and compatible Barco diagnostic displays, it delivers a new level of graphical performance, connectivity, workflow flexibility supported by Barco's Intuitive Workflow Tools, and peace of mind backed by a 5 year all inclusive warranty— making it well suited for diagnostic reading environments.

Designed for radiologists, pathologists, and other clinical users who need a flexible workstation setup across locations, Barco eGPU Solution enables a consistent connection experience between laptop, display controller, peripherals, network access, and Barco displays. It supports efficient workstation deployment for remote and hospital-based reading environments, while helping maintain a familiar imaging workflow.

Single-cable, high-performance workstation setup

By connecting the Barco eGPU Solution via Thunderbolt™ 4/5, you benefit from high data transfer speeds of up to 80/120 Gbps and a powerful single-cable workstation connection. The solution integrates the Barco MXRV-3100 display controller in an external enclosure, enabling compatible Windows laptops to connect to Barco diagnostic displays with the graphical performance required for demanding image intensive workflows.

The solution also provides extensive connectivity options — including USB-A, USB-C, Ethernet, and DisplayPort connectivity via the MXRV-3100 — helping create a complete, efficient, and flexible workstation setup with minimal configuration effort.



Compatible with Barco displays and Windows laptops

The Barco eGPU Solution is compatible with Barco diagnostic displays and validated for Windows laptops with Thunderbolt™ 5. This enables IT teams to deploy flexible reading workstation setups without the need for complex desktop configurations.

With QAWeb Enterprise, the quality assurance and compliance status of connected displays can be managed remotely. This helps IT and imaging teams maintain visibility across display fleets, including displays used in remote or distributed workstation environments.

Flexible workstation support for remote reading

Remote reading continues to become an important part of modern imaging workflows. Barco eGPU Solution supports this evolution by enabling a compatible laptop to connect through a single cable to a high-performance display workstation setup, including Barco displays, peripherals, network access, and the MXRV-3100 display controller.

This makes it easier to support flexible workstation configurations for use cases such as home reading, on-call duties, evening work, and distributed reading environments — while keeping the technical setup consistent with imaging workflows.

Please consult your Barco representative or local distributor to confirm product availability in your region. References to products or services do not guarantee availability in all locations.

Technische Daten

EGPU SOLUTION

General specifications eGPU Enclosure

Connectivity	1 x Thunderbolt™ 5 upstream port with 96W power delivery 1 x Thunderbolt™ 5 downstream port with 15W PD 1 x internal PCIe (x16) slot with 4 lanes PCI Express 4.0 interface 1 x USB 3.2 Gen2 Type C (10Gbps, 15W/port) 3 x USB 3.2 Gen2 Type A (10Gbps, 7.5W/port) 1 x 2.5 Gigabit Ethernet
Ethernet	Support 2.5Gbps/1000Mbps/100Mbps/10Mbps LAN speed, fully compatible with IEEE 802.3, IEEE 802.3u, and IEEE 802.3ab, IEEE 802.3bz, IEEE 802.3x
Power delivery Thunderbolt port	96W
Internal power supply	850W ATX Power supply Unit
Chassis Dimension	346 x 170 x 77 mm
Weight	6,164 g (without GPU)

General specifications MXRV-3100

Bus compatibility	PCI Express Gen4 x8
Power consumption	50 Watt
Form factor	2.713 inches x 6.137 inches, single-slot
Platforms	Intel® and AMD architectures
Power Connector	No external power connector
Graphics accelerator	NVIDIA® Ampere® GA107
Display memory	GDDR6 4GB
Memory bandwidth	96 GB/s
Pixel depth	32-bit pixels (supports 8-bit and 10-bit per color channel)
Electrical standard	DisplayPort v1.4 (uncompressed)
Direct3D hardware support	DirectX 12.07, Shader Model 5.17, Vulkan 1.2
OpenGL hardware support	OpenGL 4.6
Connectors	4x Mini DisplayPort
Connectivity	Native DisplayPort suggested
Operational temperature	0° to 50°C ambient

General specifications eGPU solution

Operating system	Windows 11, 64-bit and above
Warranty	5-year all-inclusive warranty and service support

General accessories

Power cord	Region specific power cord based on the ordered Barco part number
Thunderbolt cable	1 x Thunderbolt™ 5(80Gbps) Cable 0.8m
Manual	1 x eGPU installation guide

Generiert am: 11 Jun 2026

© 2026 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.