

MNA-420 ENC SDI

HD AV-to-IP adapter for the OR and hybrid OR



- AV-to-IP conversion
- 2 x FHD resolution
- Medical-grade
- Established 3rd generation technology

Adapter for the operating room

The MNA-420 ENC SDI converts 2 3GSDI video signals to Nexxis RAW IP packets. Other non-video signals such as audio and USB for keyboard/mouse are also supported. End-to-end video latency is amazingly low and is guaranteed not to exceed a single frame.

Capabilities

The MNA-420 adapters are part of Barco's Nexxis solution, which provides users with uncompromised networked visualization for the digital operating room. The compact Nexxis AV-to-IP adapters offer simplicity and flexibility while maintaining the highest possible performance standards and fitness for use in demanding medical environments.

As a third generation device, the MNA-420 ENC SDI provides the full richness of the established Nexxis platform while:

- increasing future scalability
- improving ease of installation
- adding increased security performance
- reducing ecological footprint

Product specifications

MNA-420 ENC SDI

General specifications

Video conversion	Converts digital video signals to uncompressed IP streams
Processing	1920x1080p60 on each of the two 3G-SDI input channels
Color depth	YCbCr 422: 8-bit / 10-bit
Latency	Subframe
Security	AES 128 encryption of all video, data & control signals
Encoder system	N/A
Video Output	N/A
Video Input	2x 3G-SDI standard BNC connector
Network output	2x HD uncompressed IP stream
IP Connectivity	1x 10GbE Fiber Optic Interface with SFP+ module
IP Standards	Zeroconf, IPv4, IGMP, DHCP, sRTP, sRTCP, 802.1q, AES 128b, HTTP(s)
USB	1x USB Type A
USB Power Output	Max. 5 V / 500 mA (2.5 W) per USB 2.0 Type-A port
Audio	Headset/Stereo line out 15mm length compatible 3.5mm TRRS jack
Compliance	N/A
GPIO	1x GPI (1x camera trigger) via 15mm length compatible 3.5mm TRRS jack
Nexxis Integration	Fully integrated in the Nexxis solution, compatible with MNA-1x0, MNA-240 and MNA-4x0 devices
NexxisPlus Integration	N/A
PSU	External 12Vdc Medical Approved PSU, 100-240VAC 50-60Hz 60W with lockable connector at DC side
Power Consumption	Maximum: 20W Typical: 8.4W
Size	35 mm H x 103 mm W x 131 mm 1.4" H x 4.1" W x 5.2" D (+/-2 mm / 0.1")
Weight	0.4 kg (0.88 lbs)
Temperature	5°C to 40°C (41°F to 104°F)
Humidity	Maximum 85%
Altitude	700 hPa
Storage conditions	Storage temperature: -20°C to 60°C (-4°F to 140°F) Storage relative humidity: 10% to 93% Storage altitude: 500 hPa
Acoustic noise level	Typical 32dBA at 20°C at 1m
Mounting	Versatile mounting bracket included
Certifications	-CB (IEC 60601-1) -CB (IEC 62368-1) -cRU, RU (cRUus) -Demko -CE medical device class I -UKCA -BIS Registration, IS 13252 (part 1)
Standards	Medical Equipment: -IEC 60601-1:2005 + A1:2012 + A2:2020 -IEC 60601-1-6:2010 + A1:2013 + A2:2020 -IEC 60601-1-2:2014+A1:2020 (Ed.4.1) -AAMI ES 60601-1:2005 + A1:2012 + A2:2021 -CAN/CSA-C22.2 No.60601-1:08 + A1:14 (Reaffirmed 2022) -EN 60601-1:2006 + A1:2013 + A12:2014 + A2:2021 + A13:2024 -EN 60601-1-6:2010 + A1:2015 + A2:2021 -EN 60601-1-2:2015+A1:2021 (Ed.4.1) -FCC class B -ICES-001 Level B ITE Equipment: -IEC 62368-1:2018 -EN IEC 62368-1:2020 + A1:2020 -IS 13252 (Part1): 2010
3D Video Support	The following video formats are supported: -1920x1080p60Hz Line-interleaved -1920x1080i60Hz Line-interleaved Level B (vp1d 0x8C) -Dual-stream 1920x1080p60Hz (using first two-SDI input channels)
Streamback	N/A

Last updated: 31 Mar 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.