

ClickShare C-5

Simple, one-click wireless presentation for huddle spaces



- **Entry-level wireless presentation model**
- **Content sharing with the ClickShare App and native BYOD**
- **Secure and cloud managed**

The ClickShare C-5 brings simple, wireless collaboration to small meeting rooms and huddle spaces. You and your guests can easily share content to the room display, with just one click in the ClickShare App, from any laptop or mobile device. It offers a full BYOD experience, including screen mirroring with Airplay, GoogleCast and Miracast.

Product specifications

CLICKSHARE C-5

General Specifications

Operating system	Windows 10 and higher macOS 11 (BigSur) and higher Android v9 and higher (ClickShare App)* iOS 12 and higher (ClickShare App)*
System requirements	For a smooth experience with Microsoft Teams or Zoom Minimum: Intel i3 dual-core processor or AMD Ryzen 7 / 8GB RAM / OS: Windows 10 latest build or Mac OS Mojave latest build Recommended: Intel i5 4-core processor or AMD Ryzen 9 / 8GB RAM / OS: Windows 11 latest build or Mac OS latest build
Video outputs	4K UHD (3840*2160) @ 30Hz. HDMI™ 1.4b or USB-C DisplayPort 1.2
Audio output	HDMI
USB	1 X USB-A, 1 X USB-C
ClickShare Buttons	0
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast
Maximum sources simultaneously on screen	1
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHz and 5 GHz
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbi 1x USB-C 2.0 (front); 1x USB-A 2.0 (front) -only Gen2: 1x USB-C 3.0 (front); 1x USB-A 3.0 (front)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Touch screen support & Interactivity	/
Room Dock (peripheral support)	No
Local view	Local view of the room display only
Network connection	LAN & WiFi
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage upon registering via SmartCare
*	* depends on configuration, available in future firmware updates
Dimensions (HxWxD)	34 mm x 135 mm x 135 mm
Power consumption	Operational: 5-10W, 24W Max
Power supply	Standard 110/220 V AC plug or USB-C
Weight	900 gr

Last updated: 09 Jun 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.