

SP4K-35

36,000 lumens smart cinema projector



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPureTM**
- **Fit and forget**

SP4K-35 is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A next-generation laser projection family for all cinema screens. The SP4K models come in many different configurations offering you the freedom of choice. A wide range of brightness options, compatibility with both Barco lenses and selected 3rd party lenses, as well as a touch display and live streaming option. Play with the available options to match your specific needs.

Brilliant image

The SP4K models of the Series 4 family brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image ManagementTM includes patented technology to guarantee sharp, consistent image quality over time.

Ready for tomorrow, today

With the SP4K models and their RGB laser lightsource, the Barco ColorgenicTM technology opens up more than 98.5% of Rec. 2020. Moreover, all SP4K models are fully enabled for future innovations like 4K 120fps and compatibility with the latest immersive audio standard.

Barco EcoPureTM

This silent running projector (51dB(A)) is fully ready for boothless operation. In addition, the SP4K-35 smartly manages its power consumption reaching projector efficiency levels up to 11.3 lumens per Watt. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plateTM spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-35 seamlessly integrates into your current setup.

Product specificaties**SP4K-35****Algemene specificaties**

Oorspronkelijke helderheid	36,000 lumens (typical)
Native contrastverhouding	2000:1 (typical) up to 3000:1 with HC lens
Digital MicroMirror Device™	3x 1.38" DC4K
Resolutie	native 4K: 4096 x 2160
Kleurengamma	DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates)
Lichtbron	Laser
Prime-lenzen	0.8; 1.01; 1.13-172; 1.35-1.86; 1.46-2.10; 1.65-2.60; 2.00-3.35; 2.53-4.98 High-brightness and high-contrast B-lenses compatible
Helderheidsstabiliteit op lange termijn	40,000 hrs @ average usage conditions
Behuizing	integrated cooling design and patented sealed optical assembly
Afmetingen (BxLxH)	projector incl. feet 760 x 1470 x 612 mm 29,92 x 57,54 x 24,09 inches
Gewicht	163kg/359lbs
Stroomvereisten	single phase or triple phase 200-240V 20A
Warmtebelasting	10,000 BTU/hr
Luchtafvoer	615CFM
Omgevingstemperatuur	40°C / 104F max.
Vochtigheidsgraad omgeving	85% RH max.
Mediaserver	Barco Alchemy ICM-P-X and other media server brands ** supported
Stroomverbruik	3.1kW (3W in Eco mode)
Geluidsniveau	51dB(A) @1m and 25°C ambient temperature
3D-systemen	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Laserclassificatie	Laser Class 1 -Risk Group 3
Gebruikersinterface	Touch Display and/or web based
Notities	** projector configuration with ICP-D; contact Barco service for the list of supported brands

Laatst bijgewerkt: 23 Sep 2026

© 2026 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com