

FLDX 0.8 - 1.21 : 1 (EN66)

Short focus



Focus range: 0.7 - 7.0 m Throw ratio

- WUXGA 0.75 - 1.13 : 1
- WQXGA/4K 0.80 - 1.21 : 1
- F80: 1.06 - 1.60 : 1 (WQXGA/4K UHD) (F80 requires lens adapter R9801442)
- F400-N4K: 0.71 - 1.06 (Requires the use of individual F400-lens adapters)

Product specifications**FLDX 0.8 - 1.21 : 1 (EN66) SHORT FOCUS****General specifications**

| | |
|-----------------|---|
| Working F/# | F 2.4-3.29 Motorized Iris F# 2.4-6.5 with memory |
| Zoom ratio | 1.51 Motorized zoom and focus with memory |
| Platforms | For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 1.06 -1.60 : 1 (WQXGA/4K UHD) |
| Shipping weight | 4.0 kg |
| Throw Ratio | DMD chip WUXGA 0.75 -1.13 : 1 WQXGA 0.80 -1.21 : 1 Image size tolerance +/-2% |
| Focal length | 15.98-23.99 mm |
| Focus Range | 0.7-7.0 m |
| Weight | 3.3 kg |

Last updated: 22 Apr 2026

© 2026 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.