

# ClickShare USB-C Extension over CAT kit



- **Extends USB 2.0 and DisplayPort™ connectivity up to 40m with a standard CAT 5e (or higher)**
- **Enables 4K content sharing**
- **Connects the ClickShare Hub Base Unit with the Control Panel or user device**
- **Powered by the Base Unit, no extra power supply required**
- **Supports laptop charging with an additional power supply**

The ClickShare CAT Extender over CAT kit makes complex meeting room installations easy by extending USB 2.0 and DisplayPort™ connectivity to 40m from the ClickShare Control Panel or meeting participant device. It supports intricate cable routing without signal loss and is powered by the ClickShare Hub—no extra power supply required. For meeting participants, it enables 4K content sharing with a wired connection and ensures uninterrupted collaboration thanks to its laptop-charging capabilities when connected to a power supply.

Expected to be available Jul 2026.

## 기술 사양

## CLICKSHARE USB-C EXTENSION OVER CAT KIT

### 일반 사양

|                      |   |
|----------------------|---|
| 시스템 요구 사항            | When connected with laptop for wired content sharing: USB 2.0/3.0, USB-C DP alt mode and PD charging  |
| Resolution           | When connects etween ClickShare Hub & Control Panel: -Cat 5e/Cat 6/Cat 6a/Cat 7: up to 1080p, 60Hz Between ClickShare Hub & Laptop for wired content sharing: -Cat 5e/Cat 6/Cat 6a/Cat 7: up to 4k, 30Hz  |
| 연결                   | TX box: USB-C Port-1: support DP signal(maximum 4k@30) and USB2.0 interface RJ45: for HDBaseT transmission, no ethernet connectivity USB-C Port-2: for external USB-C power adapter RX box: USB-C: support DP signal(maximum 4k@30) and USB2.0 interface RJ45: for HDBaseT transmission, no ethernet connectivity                                 |
| 온도 범위                | Operational: 0°C~40°C Storage: -40°C~85°C   |
| 습도                   | Operational: 85% non-condensing Storage: 95% non-condensing   |
| 보증                   | 1 year  |
| 치수(HxWxD)            | 122 * 152 * 34 (mm)   |
| 소비전력                 | Between ClickShare Hub & Control Panel: TX box: 19.894W / RX box: 4.623W Between ClickShare Hub & Laptop for wired content sharing: TX box: 4.621W / RX box: 5.615W   |
| 중량                   | TX box: 333g RX box: 315g   |
| Box content          | TX box, RX Box, 1.2M USB-C to USB-C cable*2, screws   |
| Resolution           | When connects etween ClickShare Hub & Control Panel: -Cat 5e/Cat 6/Cat 6a/Cat 7: up to 1080p, 60Hz Between ClickShare Hub & Laptop for wired content sharing: -Cat 5e/Cat 6/Cat 6a/Cat 7: up to 4k, 30Hz  |
| Maximum cable length | Between ClickShare Hub & Control Panel: -Cat 5e/Cat 6: up to 60m -Cat 6a/Cat 7: up to 70m Between ClickShare Hub & Laptop for wired content sharing: -Cat 5e/Cat 6: up to 35m -Cat 6a/Cat 7: up to 40m  |
| Power                | Connected to ClickShare Hub & Control Panel: TX and RX power from ClickShare Hub Core/Pro Connected to ClickShare Hub & laptop: TX power from laptop, RX power from ClickShare Hub Core/Pro Connected to ClickShare Hub & laptop, with an external PSU: TX power from external USB-C power adapter (>100W), RX power from ClickShare Hub Core/Pro |
| Compatibility        | For connection between Base Unit and Control Panel: ClickShare Hub Core/Pro For wired content sharing: ClickShare Hub Core/Pro, ClickShare CX-50 Gen2, ClickShare Bar Pro   |
| Mounting             | Mounting holes build-in the housing for desk, ceiling or wall.  |

작성일: 01 Jun 2026

© 2026 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 [www.barco.com](http://www.barco.com)을(를) 확인하세요.