


D310



- -

3 to 2 and 2 to 2 Pull Down (patented Motion Picture Processing)-Time Based Correction-Video Equalizing (3-Band)-
Dynamic Image Stabilization-
Digital Brightness/Saturation Control-Scaler/Compressor-
Automatic RGB Matrix Selection-
Analytical Contrast Rendering (Stretch to SubBlack,
Gamma (RGB))-Luminance Tracking-
Dynamic Sample Weight Distribution

일반 사양

호환성	-All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43 in Composite, S-VHS, RGB or Component format) -All computer graphics up to SVGA (800 x 600) -All Macintosh computers (640 x 480) -Pannellink loop through data signal
입력	-Two Composite Video inputs on BNC connectors -Two S-video inputs on 4 pin mini-Din connectors -Once Component Video input (R-Y, B-Y, Y, sync) on 4 x BNC connectors -One RGBs or RGsB input on 4 x BNC connectors -One Pannellink input
출력	-Pannellink data output -Long/Short Distance digital link -RGBs or RGsB output on HD15 connector (monitor) -RS 232 loop-through communication port on D9 male & female connectors -RS 485 Phoenix connectors for AX Link

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.

