

SLM R10 Executive



技术规格

SLM R10 EXECUTIVE

一般规格	
光输出	10000 ANSI lumens
数字微镜器件	three S-XGA DMDs (1280 x 1024)
亮度均匀性	亮度一致性: >总屏幕的90%
分辨率	1280 x 1024 (native) 1600 x 1200 (max)
灯泡	2.2 kW Xenon illumination system Typical lifetime: 500 hours Max. lifetime: 1000 hours
对比度	> 800:1 (High Contrast Mode: >1600:1)
屏幕宽度	5m -15m / 6 ft -50 ft
兼容性	<ul style="list-style-type: none">All video sources in Composite, S-VHS, Component or RGB formats or serial digital formatAll currently proposed HDTV, extended and improved television standardsMost Macintosh computersComputers and electronic workstations with a resolution up to 1600 x 1200 pixelsTwo digital input slots allow direct digital interfacing with current and future digital inputs
镜头	提供的定焦镜头投射比率为0.8:1 (超短投射比率, 专为后屏幕同轴投影设计) 或1.2:1 (长投射)。 电动变焦镜头的投射距离为屏幕宽度的1.6-2.0、2.0-2.8、2.8-5.0、5.0-8.0倍
输入	2 x multifunctional 5-Cables input (high bandwidth) for the connection of: -RGB analog signals with standard sync (BNC) or tri-level sync, sync on green or separate sync -Standard video signals -S-VHS signals 2 x DVI in + 1 x DVI out SDI loop-through (Serial Digital Input) Video input
可选	SDI loop-through (Serial Digital Input) HD-SDI loop-through (High Definition Serial Digital Input)
通信	1 x D9 connector for RS232 or RS422 loop-through 1 x D9 connector for peripherals 1 x 3-pin male XLR connector for wired remote network connection
噪音级别	< 56 dBA
功率消耗	2750 W
电源	220 V (公差 200 V - 240 V)
安全级别	Compliant with UL1950 and IEC950
网络连接	Optional
特性	· Picture-in-picture · Seamless source switching with effects
尺寸(宽x长x高)	529 x 795 x 429 mm (20.8 x 31.3 x 16.9 inch)
镜头移动	TLD Lenses Motorized V shift: -20% +100% Motorized H shift: max. 65% (L+R) For specific details per lens type: see lens product pages
无缝切换	Standard
ScenergiX	Standard
封装DLP™内核	Not available
净重	45 kg (99lbs)

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。