


ILite 6 BK

6mm pixel pitch, 2,000 nits surface-mounted LED tile



6mm
PIXEL PITCH



Thanks to its attractive price-performance ratio, Barco's ILite 6 BK is a smart choice for events and indoor installations that require a modular and thin LED tile. What's more, it is easily and quickly serviceable. The high-class LED technology makes sure that your overall image consistency remains excellent, even when tiles are added to or removed from the display.

Complete rental solution

The ILite 6 BK has been designed with the road in mind and features easy set up, simple serviceability (OSD, Tiles swap) and upgradeability. As a complete rental solution, it includes rugged rental structures, sturdy flight cases and the new DX-700 which allows you to have your display installed in no time.

Cross-rentable

Thanks to Barco's renowned color calibration technology, the ILite 6BK tiles are fully cross-rentable. This technology allows you to mix and match tiles of different batches and various run-time ages to obtain a seamless display with a perfect image every single time. The ILite 6 BK is also compatible with the complete range of existing ILite peripherals and sources.

Best price-performance

ILite can be used in all indoor environments and offers you the best visual performance for a minimum investment, hereby ensuring maximum return on investment.

Product specificaties**ILITE 6 BK****General specifications**

Pixelpitch	6.22 mm
Helderheid	2,000 nits
Led-configuratie	3-in-1 SMD
Pixel dichtheid	25,829/sqm 2,402/sqf 5,184/tile (72x72)
Hor. kijkhoek	120° (min 50% brightness)
Vert. kijkhoek	+60, -60° (min 50% brightness)
Contrastverhouding	3,000:1 (at 500 lux)
Levensduur	45,000 hours to 50% of initial brightness
Energieverbruik	335 W/tile (max) 156 W average
Netspanning bij gebruik	200-240V / 50-60Hz
Paneelafmetingen	Width: 448mm Height: 448mm Depth: 150mm
Gewicht / tegel	14.3 kg
IP-classificatie	Indoor use only
Verwerking	14 bit/color
Kleuren	4.4 trillion
Vernieuwingsnelheid	400Hz
Opbouw voet	Max. 12 tiles high
Opbouw truss	Max. 15 tiles high
Link-interface	DVI interface (DVI connector)
Max. lengte link	4.5m (with Barco DVI cable)
Interfaces	2x DVI link
Max. stroomcascadeschakeling	6 tiles
Onderhoudsgemak	Back
Bedrijfstemperatuur	0-40°C
Opslagtemperatuur	-20 -60°C
Operationele vochtigheid	35-85%
Vochtigheid bij opslag	10-90%
Broncompatibiliteit	CVBS, YC, YUV, RGB, DVI, SDI, HDSDI (with DX700: and Dual link DVI, Dual link HDSDI)
Bedienbare digitizer	DX-700 (with DVI output card), D320, LEDPRO
Certificeringen	CE classA, TUV, FCC, Class A, ETL, RoHS

Laatst bijgewerkt: 10 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.