

# UDM-4K30

27,000 lumens, 4K UHD, 3-chip DLP digital large venue projector



- **Most compact and lightest laser projector in the 30K lumen category**
- **Robust design made for the toughest conditions**
- **Extremely flexible with widest lens shift and modular design**
- **Best-in-class 4K UHD processing at lowest latency with Barco Pulse Single Step Processing**
- **Remote fleet management & connectivity with Barco Insights Management Suite**

Weighing less than 50kgs, this is the lightest projector in its category. And while the compact and light-weight design of the UDM-4K30 saves you lots of installation time and reduces shipping and labor costs, it never compromises on the quality or brightness of your projection. The UDM-4K30 features 4K UHD resolution to deliver impactful 4K experiences with mind-blowing colors. The UDM projector offers the widest color spectrum for 30K laser phosphor projection on the market outperforming the Rec. 709 color space.

## Operational efficiency

Lift your creativity to unprecedented levels with the widest lens shift on the market and an extensive list of other peripherals which will facilitate a smooth installation and integration of the projector in your setup. Barco's unique FLEX2 feature allows you to tune and lock the brightness level or resolution for a specific show. The modular design supports fast maintenance and easy serviceability in the field.

## Pulse Electronics

The UDM is built on the unified Barco Pulse electronics platform. With its proprietary Single Step Processing technology warping, scaling and 4K UHD processing is done in only one step. The result? Razor-sharp images, market leading lowest latency, and less dark time than comparable solutions.

## Connectivity

The UDM is the first projector in the Barco range which is fully connected. The Barco Insights Management Suite Dashboard and remote log file access enables faster and more effective troubleshooting. Manage the brightness



settings of your projector fleet and keep track of operating conditions anywhere and anytime through a secured cloud-based platform and integrated 3G connectivity.

### **Long lifetime**

Thanks to its robustness and built-in dust and pollution filter, you can trust UDM to withstand the endurances of life on the road. With the laser phosphor light source, lamp-related costs and maintenance as well as image flicker, belong to the past. Barco's outstanding integrated laser cooling prevents overheating and the Constant Light Output functionality guarantees constant brightness and color across the projector's lifetime.

**Product specificaties****UDM-4K30**

General specifications	
Opmerkingen	
Type projector	4K UHD 3-chip DLP digital projector
Technologie	0.9" DMD™ x3
Resolutie	3,840 x 2,400 (4K UHD) / 2,560 x 1,600 (native) / 5,120 x 3,200 (processing)
Helderheid	25,000 ansi lumens / 25,500 center lumens / 27,000 ISO lumens*
Contrastverhouding	Full field 2000:1 / Barco Dyna Black 20000:1
Helderheidsuniformiteit	95%
Beeldverhouding	16:10
ScenergiX	Horizontal and vertical edge blending
Lenzen	TLD+ 0,37; 0,65-0,85; 0,8-1,16; 1,25-1,6:1; 1,5-2,0:1; 2,0-2,8:1; 2,8-4,5:1; 4,5-7,5:1; 7,5-11,5:1
Optische lensverschuiving	Vertical between -100% to +130%, depending on lens Horizontal up to +/-40%, depending on lens Motorized zoom and focus (with lens memory on TLD lenses) Motorized lens shift (with position memory on all lenses)
Kleurcorrectie	P7
Lichtbron	Laser B + Red compensator and inorganic Ph wheel
Levensduur lichtbron	20,000hr (at 100% laser power, DynaBlack = off)
Optische dowser	Digital
Foto-na-foto	Two sources simultaneously
Verzegelde DLPT™-kern	Standard
Oriëntatie	360°
DMX 512	Standard
WARP	Direct adjust OSD + toolset
Beeldverwerking	Embedded warp & blend
Verwerking	Pulse Electronics
Trapeziumcorrectie	Yes
Geïntegreerde webserver	Yes
CLU (constante lichtuitvoer)	Standard
3D	Active eye wear (optional), passive circular (optional); 2 flash up to 200Hz; optional Dual Eye Point 240Hz
Ingangen	Single HDBaseT; HDMI2.0 (HDCP2.2, HDR10); DP 1.2 (HDCP1.3); Quad 3G/12G SDI/BarcoLink ULTRA
Optionele ingangen	Quad DP1.2, Fiber SFP
Invoerresoluties	From NTSC up to 4K (4,096 x 2,160) Refresh rates: 24hz to 120hz 4K/4KUHD (4096 x 2160 / 3860 x 2400) to 240hz WQXGA (2560 x 1600)
Max. pixelklok	600 Mhz
Softwaretools	Projector Toolset + Android** app + iOS** app

**Product specificaties****UDM-4K30**

Controle	XLR wired + IR, RS232, Wifi**, GSM**
Netwerkverbinding	10/100 base-T, RJ-45 connection, Wifi**
Voedingsvereisten	120-160 V (max 70% brightness) 18.5A / 200-240V (+/-10%), 13.5A, 50-60Hz
Max. energieverbruik	1900W nom/ 2200w max @ 230 volts ECO STBY 1300W nom/ 1530w max @ 120 volts ECO STBY
Geluidsniveau (standaard bij 25°C/77°F)	49 dB(A)
Operationele omgevingstemperatuur	0-40°C / 32°-104°F ***
Operationele vochtigheid	0-80% (non condens)
Dissipatie BTU	Max. 7000 BTU/h
Afmetingen (B x L x H)	725 x 540x 339 mm / 28.54 x 21.26 x 13.3'
Verzendingsafmetingen	incl. pallet  (WxLxH) 850 x 665 x 613 mm / 33.46 x 26.18 x 24.13 inches
Gewicht	48 kg (105lbs) / shipping weight from factory: 61 kg (134.5 lbs)
Standaardaccessoires	Power cord, wireless/XLR wired rugged remote control
Certificeringen	Compliant with UL60950-1 and EN60950-1, complies with FCC rules & regulations, part 15 Class A and CE EN55032 Class A, Rohs
Garantie	3 years
*Opmerking	*Brightness levels +/-10%  ** Wifi and GSM options are not available in all countries. Check with your Barco representative for more info.  ***at higher altitude light output might be dimmed

Laatst bijgewerkt: 17 May 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.