

SLM G5 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



- Enhanced low-light video performance is the result of its newly designed pixel map processor.
- Integrated Constant Light Output (CLO), which can be linked with other G5 projectors for use in multi-screen applications.
- True seamless switching includes transition effects such as cross-fade, wipe, etc.
- Carrying handle with integrated rigging system.
- The unique "click-and-play" lenses make it possible to exchange lenses in seconds.
- Direct stacking and interlocking design enable an easy and stable setup
- Sealed optics significantly reduce optical system maintenance, which allows the G5 to be used at events where smoke generators are involved.
- Modular structure provides greater accessibility to serviceable parts.
- The optical system's compact and lightweight lens range is designed for the continuing evolution of the DLP technology.

Technische Daten**SLM G5 PERFORMER**

Allgemeine technische Daten	
Lichtausgabe	5.000 ANSI lumens
Auflösung	1024 x 786 (native) 1600 x 1200 (max)
Auflösung	1024 x 786 (native) 1600 x 1200 (max)
DMD™-Chip	3 high resolution XGA DMD's
Helligkeitsgleichförmigkeit	> 90% for the total screen area
Kontrast	500:1 (full white/full black) 500:1 (full white/full black)
Lampe	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp Power: 1,2 kW
Geräuschpegel bei 20°C	< 43
Geräuschentwicklung (bei 40 °C -104 °F)	< 50
Netzspannung	110/230 V
Stromverbrauch	1.600 W
Umgebungstemperatur	40°C (104F) max
Größe	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Gewicht (einschließlich Verspannvorrichtung)	56 kg / 124 lbs
Optiken	BARCO's "click-and-play!" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
Lens Shift	Motorized V shift: up to 118 % Motorized H shift: up to 65 %
Gekapseltes optisches System	Yes
Nahtloses Umschalten	Standard
ScenergiX	Standard
Feste Eingänge	<ul style="list-style-type: none">• 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals• 2 Multistandard DVI• SDI input (Serial Digital Input)
Optionale Eingänge	One free digital input slot for optional input modules: <ul style="list-style-type: none">• SDI• HD -SDI
Fernbedienung	<ul style="list-style-type: none">• RS232 or RS422 loop-through input (D9-connector) for PC based projector control• Communication input (D9-connector) for peripherals• 3 pin male XLR connector for wired remote (standard remote)• 3 pin female XLR connector for bi-directional communication (rugged remote)

Generiert am: 15 Mar 2023

Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät. Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern. Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.