

D-Cine Premiere DP90P

Dedicated Post Production projector



Technische Daten

D-CINE PREMIERE DP90P

Allgemeine technische Daten

DMD™-Chip	3 x 1.2" dark metal type Advanced DLP Cinema™ signal processing with built-in 3D look-up table
Panel-Auflösung	2048 x 1080
Gehäuse	Hermetically sealed optical engine (DMD™ + prism)
Lichtausgabe	4500 centerlumen
Montage	Standing or ceiling mounted Up to 7 degrees tilt via projection head
Lampe	1.5k to 4.0k Xenon arc lamp sizes Compatible with standard and high performance lamp types
Helligkeitsgleichförmigkeit	Exceeds the DCI and SMPTE draft recommendations (> 75%)
Kontrast	2500:1
Digitale Video-Eingänge	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Standards	Motorized lensholder CLO software
Primärobjektive	M25 1.25 -1.45:1 / M25 1.45 -1.8:1 / M25 1.8 -2.2:1 / M25 2.2 -3.0:1 zoom and M25 3.0 -4.3:1
Farbskala	Exceeds the current DCI and SMPTE recommended color space
Farben	Native color points: native red: x = 0.7 y = 0.3 native green: x = 0.2 y = 0.76 native blue: x = 0.145 y = 0.040
Projekordiagnose	Via touch screen Via D-Cine Communicator control software Post production edition standard with every product Via SNMP agent
Stromversorgungsanforderungen	1 x 220V max. 17,000 BTU/hr (with 4kW lamp)
Abmessungen	projector: 640(H) x 730(W) x 1170(D) mm / 24.2(H) x 28.7(W) x 46.1(D) inch powerbox: 295.3(H) x 329.5(W) x 473.7(D) mm / 14.6(H) x 13.0(W) x 18.6(D) inch
Gewicht	projector: approx. 120kg (265lb) powerbox: approx. 20kg (44lb)
Optionen	■ Anamorphic lens fitting for 1.25:1 scope lens ■ Acsar 2 Alternative Content Input Processor ■ ImagePRO HD ■ SNMP agent (v3)
Bestell-Information	R9004441

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.