

OV-501

Entry level 50" single lamp video wall system integrating DLP™ technology with XGA resolution



Product specificaties

OV-501

General specifications	
Resolutie	XGA (1024 x 768px)
DMD-chip	1024 x 768px 0.7" ±12° tilt DDR MTBF: 650,000 hours Lifetime: 100,000 hours
Aantal gebruikte microspiegels	0.8 M
Pixelvorm	Square
Beeldverhouding	4:3
Lamp	Lamp life (lamp manufacturer specs @ IEC 61947-1 test conditions): ■ 100W: 10,000 hours
Wisselstroom	100-240 VAC, 60-50Hz
Vermogen	190 W
Warmteafvoer	650 BTU/h
Helderheid	550 (typ.) (@ 6500K, but can be set to other values)
Contrast	1300:1
Helderheidsuniformiteit	85% (ANSI Points)
Dimmen	Optical Dimming with Dynamic Feedback Brightness locking: 50-100% optical dimming range, without color shift, loss of contrast and loss of colordepth
Kleur	EBU color triangle White point: 6500 K (can be set to other values)
Ingangen	Standard: DVI-D in/ DVI-D out with dual XGA support Optional (only in single XGA mode, sdi input upon request): OverView D Multi input module: DVI-D, DVI-I, Multi Sync RGB input (VGA upto UXGA), Video Input (PAL, NTSC, SECAM)
Genlock	48 – 62 Hz
Afmetingen structuur	Diagonal: 50" nominal Width: 1,000 mm / 39.6 in. Height 750 mm / 29.5 in. Footprint n.a. Depth: 664.5 mm / 26.2 in. Socket Height: 875 -1,000 -1,200 mm / 34.5 -39.4 -47.2 in. Socket Height: (min) 455 mm / 17.9 in.
Gewicht	62 kg (excl. structures)

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

