

iQ G400



Technische Daten

IQ G400

Allgemeine technische Daten

Lichtausgabe	4,200 ANSI lumen
Helligkeitsgleichförmigkeit	Brightness uniformity: >95 % for the total screen
LCD-Panels	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
Auflösung	1024 x 768 (native)
Lampe	2x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 1000 h/lamp. 1000 hours in Dual Lamp Mode or max. 2000 hours/set in Single Lamp Mode.
Optiken	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8,1.9-2.6,3.0-6.0 times the screen width
Bildgröße	From 1-6 m/3-20 ft.
Kontrast	>400 : 1 (full white/full black)
Frequenzen	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Merkmale	• Advanced picture-in-picture • Seamless switching with effects • Standard cable basket • Standard light shutter • Advanced digital zoom
Kompatibilität	The iQ G400 is compatible with: • All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats • All currently proposed HDTV, extended and improved television standards (1080i, 720p) • All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA • Most Macintosh computers • Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz • Most computer sources with a pixel clock up to 160 MHz • DVI sources up to SXGA
Eingänge	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
Abmessungen (BxTxH)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
Kommunikation	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Geräuschpegel	
Stromversorgung	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Stromverbrauch	Max 620 Watt
Wärmeabgabe	Max 2117 BTU/h
Gewicht	Net weight: Body only 12.9 kg / 28.5 lbs. Shipping weight: • without lens max.17.5 kg / 38.5 lbs. • with lens: max.20 kg / 44 lbs.
Lens Shift	QVD Lenses Motorized V shift: -30% +120% For specific details per lens type: see lens product pages
Nahtloses Umschalten	Standard
Netzwerk-Verbindung	Refer to iQ Pro G400

Generiert am: 09 Jul 2024

© 2024 Barco nv. Alle Rechte vorbehalten. Die vollständige oder teilweise Reproduktion ohne schriftliche Genehmigung ist nicht gestattet. Alle Markennamen und Produktnamen sind Marken, eingetragene Marken oder Handelsnamen ihrer jeweiligen Inhaber. Aufgrund fortlaufender Innovationen können sich Informationen und technische Spezifikationen ohne vorherige Ankündigung ändern. Die neuesten Spezifikationen finden Sie unter www.barco.com.