

# Infinipix® NP100

Image processor for LED displays



- **Processes and transmits connected video sources**
- **Manages one or more connected display(s)**

The Infinipix® NP100 processor is the next generation in LED display processors. It ensures processing and transmission of connected video sources and manages one or more connected display(s) – comprising a number of Infinifix™ transceiver cards. The NP100 is controlled via the Infinipix® NM100 manager.

**Product specificaties****INFINIPIX® NP100**

General specifications	
3D-synchronisatie	<ul style="list-style-type: none"> <li>Currently not supported</li> </ul>
Afstandsbediening	2x Ethernet: RJ-45 connectors, running 1GbE used as control protocol link to a separate Infinipix™ Manager (NM100) for centralized management of multi-device Infinipix™ Processors (NP100) and one or more Displays.
Uitgangen	<p>2x Ethernet (ULP) Modular Display Outputs:</p> <ul style="list-style-type: none"> <li>RJ-45 connectors, running 1GbE</li> <li>Uses 1000Base-T Cat 5E or Cat 6 cable with a maximum length of 100m (328 ft.).</li> </ul> <p>2x Ethernet (SFP) Modular Display Outputs:</p> <ul style="list-style-type: none"> <li>SFP+ cages supporting 1GbE or 10GbE SFP+ modules</li> <li>Uses 1000Base-T: using Cat 5E or Cat 6 cable with matching SFP+ module with a maximum length of 100m (328 ft.).</li> <li>Uses 1000Base-SX: using multi mode fiber of type OM2 of maximum 220m (721 ft.) or OM3 (Recommended) of maximum 500m (1640 ft.) with matching SFP+ module.</li> <li>Uses 10GBase-SR: using multi mode fiber of type OM3 with a maximum distance of 300m (984 ft.)</li> </ul> <p>Using 1GbE and 10GbE outputs at the same time on one device is not supported</p>
Afmetingen (B x D x H)	216 x 286 x 70 mm (8.5 x 11.25 x 2.75 in)
Video-ingangen	<p>1x HDMI (type A) Input:</p> <ul style="list-style-type: none"> <li>Formats RGB 4:4:4 and YCbCr 4:2:2 and 4:4:4; resolutions up to 2,560x1,600 @60Hz to a maximum pixel rate of 268MHz (Please consult your modular display hardware specification for its maximum supported input frequency which may be less than what is supported by the NP100 Infinipix Processor).</li> <li>Supports input bit depth of up to 12 bits per color channel</li> <li>Performs image processing at minimum of 12bits per color channel</li> <li>Other video formats supported: Single-link DVI digital sources using a DVI to HDMI passive cable converter* / DisplayPort sources using a DisplayPort to HDMI active cable converter* / VGA sources using VGA to HDMI active cable converter* / Composite, Component, S-Video sources using active cable converter* to HDMI. *: none of the cable converters are shipped with the product.</li> <li>EDID version 1.3 compatible</li> <li>Not supported: CEC</li> <li>Both progressive and interlaced sources are supported</li> </ul> <p>1x 3G SDI Input:</p> <ul style="list-style-type: none"> <li>75 ohm BNC connector, supporting formats SD-SDI per SMPTE 259M-C (NTSC/PAL resolution); HD-SDI per SMPTE 292M, 296M; and 3G-SDI per SMPTE 425M</li> <li>Dual link HD-SDI (pair SMPTE 292 links) by SMPTE 372M NOT supported</li> </ul>
Videolusuitgangen	<ul style="list-style-type: none"> <li>1x HDMI Loop Output: type A connector; HDMI input signals reproduced on HDMI Loop Output limited to a maximum pixel rate of 225MHz</li> <li>1x 3G SDI Loop Output: 75 ohm BNC connector; SDI input signals reproduced through SDI Loop output</li> <li>HDCP is not supported on loop out</li> <li>Video loop outputs are intended primarily for troubleshooting purposes</li> </ul>
Gewicht	2.72 kg (6 lbs)
Behuizing	metal
Aparte behuizing	<p>rack shelf for side-by-side Infinipix™ Manager (NM100) and Infinipix™ Processor (NP100)</p> <ul style="list-style-type: none"> <li>Width: 19" rack</li> <li>Height: 2RU</li> <li>Type: Metal</li> </ul>
Omgevingstemperatuur	Operational: 0-40° Celsius (32-104° F)
Omgevingsvochtigheid	Operational: 10-85%, non-condensing
Type voeding	100-240 VAC, 1.5A -50/60Hz
Energieverbruik	60 Watt
Standaarden	FCC: Part 15, Subpart B Section 15.107 & 15.109, Class A; CE: CISPR 24/ EN 55024, CISPR 22/ EN 55022 Level A, EN 61000-3-2 with A1, A2 2006 (only if 75W or above), IEC/EN/UL 60950-1, c-UL CSA C22.2 60950-1; ICES-003 Class A v4
Certificeringen	CE, ETL, RoHS, China RoHS, WEEE
Garantie	Full three-year parts and labor warranty

Laatst bijgewerkt: 17 May 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg [www.barco.com](http://www.barco.com) voor de meest recente specificaties.