

FLM HD14

14,000 lumens, 1080p HD three-chip DLP projector



14K
LUMENS

full HD
1920 X 1080P



Product specificaties**FLM HD14****General specifications**

Type projector	Full HD three-chip DLP digital projector
Technologie	0.95" DMD™ x3
Resolutie	1920x1080
Helderheid	14,000 center lumens 13,250 ANSI lumens
Contrastverhouding	2,100:1 2,700:1 (high contrast mode)
Helderheidsuniformiteit	90%
Beeldverhouding	16:9
ScenergiX	Horizontal and vertical edge blending
Type lens	TLD+
Lenzen	TLD+ 0.73:1 1.2:1 1.25-1.6:1 1.5-2.0:1 2.0-2.8:1 2.8-4.5:1 4.5-7.5:1 7.5-11.5:1
Optische lensverschuiving	Vertical: -10% to +110% Horizontal: -50% to +50% (on zoom lenses)
Kleurcorrectie	P7
Lampen	3kW xenon
Levensduur lamp	1,000 hours
Transport met lamp	Yes
Lampbehuizing, snelle vervanging	Yes
Lampvervanging door klant	Yes
Lampgarantie (vervanging op locatie/in de fabriek)	90 days, 500 hours / pro rata 750 hours
Verzegelde DLP™-kern	Standard
Optische dowser	Standard
Picture-in-Picture	Two sources simultaneously
Oriëntatie	table -ceiling -side (portrait) -vertical
DMX 512	Optional
WARP	Preset values + custom
Geïntegreerde webserver	N/A
CLU (constante lichtuitvoer)	Standard
Geschikt voor 3D (optioneel)	Passive Infitec
Ingangen	DVI(HDCP); 5-BNC RGBHV (RGsB/RGsb, YUV CS/SOY, Composite video, S-Video); SDI/HDSDI
Optionele ingangen	DVI(HDCP); 5-BNC RGBHV (RGsB/RGsb, YUV CS/SOY, Composite video, S-Video); SDI/HDSDI
Invoerresoluties	From NTSC up to UXGA (1600x1200) incl. HD (1920x1080)
Max. pixelklok	165 MHz
Softwaretools	Projector Toolset
Controle	XLR wired + IR, RS232
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	220-240V / 50-60Hz
Max. energieverbruik	3100W
Geluidsniveau (standaard bij 25°C/77°F)	56dB(A)
Operationele omgevingstemperatuur	0-40°C / 32°-104°F
Operationele vochtigheid	0-80% (non condens)
Dissipatie BTU	max 10577 BTU/h
Afmetingen (B x L x H)	707 x 1025 x 548mm 27.83 x 40.35 x 21.57 inches
Gewicht	99kg (218.25lbs)
Verzendingsafmetingen	(LxWxH) 1200 x 980 x 760 mm 47.24 x 38.58 x 29.92 inches
Verzendgewicht af fabriek	151kg (333lbs)
Standaardaccessoires	Power cord, wireless/XLR wired rugged remote control
Certificeringen	Compliant with UL1950 and EN60950 complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A, RoHS
Garantie	2 years

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.