

IO 网关

使用 IPMX/2110 开放标准的 AVoIP 转码器



- 设备和维护更少
- 基于标准的工作流程实现互操作性和灵活性
- 高品质且低延迟

巴可 IO-H1 和巴可 IO-H25

巴可 IO 转码器是简化的面向未来的 AVoIP 设置的基础，可将您当前的 HDMI 信号（高达 4K60 4:4:4）传输到基于开放标准的系统，延迟时间最低。

减少对额外切换器、电缆、转换器等的需求，只需添加 IO 解决方案即可从包含多个 AV 信号和控制的单个双向电缆解决方案进行转换和路由。它显著减少了杂乱和成本。

巴可 IO 编码器/解码器是一个基于网络的系统，可以容纳大量设备，并按照开放标准运行，使 A/V 集成更易于访问、更灵活且更易于维护。

每个巴可 IO-H1 套件包括：

- IO-H1 1GbE 通过 Cat5 编码器/解码器
- JPegXS
- 电源
- Quick Mount™ 板
- 安装支架

每个巴可 IO-H25 套件包括：

- IO-H25 10/25GbE 通过光纤
- JPegXS
- 电源



- Quick Mount™ 板
- 安装支架

巴可 IO-S25

巴可 IO 转码器是简化的面向未来的 AVoIP 设置的基础，可将当前的 12G SDI 信号（高达 4K60 4:2:2）传输到基于开放标准的系统中，延迟时间最低。

减少对额外切换器、电缆、转换器等的需求，只需添加 IO 解决方案即可从包含多个 AV 信号和控制的单个双向电缆解决方案进行转换和路由。它显著减少了杂乱和成本。

巴可 IO 编码器/解码器是一个基于网络的系统，可以容纳大量设备，并按照开放标准运行，使 A/V 集成更易于访问、更灵活且更易于维护。

每个巴可 IO-S25 套件包括：

- IO-S25 10/25GbE 通过光纤
- JPegXS
- 电源
- Quick Mount™ 板
- 安装支架

注意

The specifications in this document are preliminary

IO-H1

- Media Bandwidth: 1 or 2.5 GbE
- Media Connector: 1 x RJ45 (copper)
- Media Networks: 1 x main, 1 x redundant
- Control Network: 1 x 1GbE Copper
- Video Inputs: 1 x HDMITM 1.4, HDMITM 2.0
- Video Outputs: 1 x HDMITM 1.4, HDMITM 2.0
- Power: PoE+, external PSU
- IPMX Profile: Profile 3, 18:1 Compression

IO-H25

- Media Bandwidth: 10 or 25 GbE
- Media Connector: 1 x SFP+ (fiber)
- Media Networks: 1 x main, 1 x redundant
- Control Network: 1 x 1GbE Copper
- Video Inputs: 1 x HDMITM 1.4, HDMITM 2.0
- Video Outputs: 1 x HDMITM 1.4, HDMITM 2.0
- Power: PoE+, external PSU
- IPMX Profile: Profile 1 (Uncompressed), Profile 2 (4:1 compression)

IO-S25

- Media Bandwidth: 1 or 2.5 GbE
- Media Connector: 2 x SFP+ (fiber)
- Media Networks: 1 x main, 1 x redundant
- Control Network: 1 x 1GbE Copper
- Video Inputs: 1 x 12G-SDI
- Video Outputs: 1 x 12G-SDI
- Power: PoE+, external PSU
- IPMX Profile: Profile 1 (Uncompressed), Profile 2 (4:1 compression)

生成于: 09 Apr 2024

技术规格随时变化, 不会事先通知。请访问www.barco.com.cn, 获取更新信息。