

BARCOVision 9200



Specifiche tecniche

BARCOVISION 9200

Specifiche generali

Compatibilità	All current video sources in composite, S-VHS, RGB or Component forms All currently proposed HDTV, extended and improved television standards All computer graphics formats up to VGA (640x480) resolution Computer signals in S-VGA (800x600) resolution All Macintosh computers in 640x480 resolution
Contrasto	>180:1 (on 5x4 B/W checker board) > 340:1 (full white/full black)
Emissione luminosa	6000 Lumen Full White 5000 ANSI Lumen
Dimensioni schermo	Min.: 1.0 m x 0.75 m (3.3' x 2.5') Max.: 15 m x 11.25 m (50' x 37.5')

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.