

# MNA-440 DEC -H

HD AV-to-IP adapter for the OR and hybrid OR with HDMI™ technology



- **IP-to-AV conversion**
- **Up to 4K resolution**
- **Medical-grade**
- **Established 3rd generation technology**

## **Adapter for the operating room**

The MNA-440 DEC -H with HDMI™ technology converts uncompressed IP video streams to HDMI 2.0 video. Other non-video signals such as audio and USB for keyboard/mouse are also supported. End-to-end video latency is amazingly low and is guaranteed not to exceed a single frame.

## **Capabilities**

The MNA-440 adapters are part of Barco's Nexxis solution, which provides users with uncompromised networked visualization for the digital operating room. The compact Nexxis AV-to-IP adapters offer simplicity and flexibility while maintaining the highest possible performance standards and fitness for use in demanding medical environments.

As a third generation device, the MNA-440 DEC -H with HDMI™ technology provides the full richness of the established Nexxis platform while:

- increasing future scalability
- improving ease of installation
- adding increased security performance
- reducing ecological footprint

## Product specifications

## MNA-440 DEC -H

### General specifications

Video conversion	Converts uncompressed IP-streams into Digital video signals.
Processing	4096x2160@60Hz on a single output channel  Or 1920x1200@60 on each of the two output channels
Color depth	RGB 8-bit
3D technology	Show one view of the 3D video flow (left eye) on a 2D display
Latency	End-to-end: genlocked subframe; not genlocked one frame.
Security	Decryption of AES 128 encrypted video, data & control signals
Video Output	2x HDMI 2.0 lockable connector
IP connectivity	2x 10GbE Fiber Optic Interface with SFP+ module
IP standards	Zeroconf, IPv4, IGMP, DHCP, RTP, RTCP, 802.1q, AES 128b, HTTP(s)
USB	2x USB Type A
Audio	Stereo line in and Headset/Stereo line out 15mm length compatible 3.5mm TRRS jack
GPIO	1x GPI + 1x camera trigger via 15mm length compatible 3.5mm TRRS jack
Nexxis integration	Supported from Nexxis 1.14 onwards, compatible with MNA-1x0, MNA-240 and MNA-4x0 devices
PSU	External 12VDC Medical Approved PSU, 100-240VAC 50-60Hz 60W with lockable connector at DC side
Power consumption	Maximum: 25W Typical: 17W
Size	35 mm H x 103 mm W x 131 mm D   1.4" H x 4.1" W x 5.2" D (+/-2 mm / 0.1")
Weight	0.4 kg (0.88 lbs)
Temperature	5°C to 40°C (41°F to 104°F)
Humidity	Maximum 85%
Storage	Storage temperature: -20°C to 60°C (-4°F to 140°F) Storage Relative Humidity: 10% to 93%
Acoustic Noise	Typical 32dBA at 20°C at 1m
Mounting	Versatile mounting bracket included
Certifications	<ul style="list-style-type: none"><li>■ CB (IEC 60601-1) Informative report</li><li>■ CB (IEC 60950-1)</li><li>■ cRU, RU (cRUus)</li><li>■ Demko</li><li>■ CE medical device class I</li><li>■ UKCA</li><li>■ BIS Registration, IS 13252 (part 1)</li><li>■ KC</li><li>■ BSMI</li><li>■ RCM</li><li>■ EAC</li></ul>
Standards	Medical Equipment: <ul style="list-style-type: none"><li>■ IEC 60601-1:2005 + Am1:2012</li><li>■ IEC 60601-1-6:2010 + Am1:2013</li><li>■ IEC 60601-1-2:2014 (ed4)</li><li>■ ANSI/AAMI ES 60601-1: A1:2012 + C1:2009/(R)2012 + A2:2010/(R)2012</li><li>■ CAN/CSA-C22.2 No.60601-1-14</li><li>■ EN 60601-1:2006 + A1:2013 + A12:2014</li><li>■ EN 60601-1-6:2010 + A1:2015</li><li>■ EN 60601-1-2:2015 (ed4)</li><li>■ FCC class B</li><li>■ ICES-001 Level B</li></ul> ITE Equipment: <ul style="list-style-type: none"><li>■ IEC 60950-1:2005 + Am1:2009 + Am2:2013</li><li>■ EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011</li><li>■ IS 13252</li></ul>

Last updated: 09 Jul 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź [www.barco.com](http://www.barco.com), aby uzyskać najnowsze specyfikacje.