

RetroGraphics 808s



- Single front surface-coated optical grade mirror
- 67" super fine pitch Fresnel/Lenticular-Blackstripe screen with very wide horizontal and vertical viewing angles
- High-definition 8" CRTs with electromagnetic focus system
- F1.1 color corrected hybrid liquid coupled lenses
- Optional built-in Video Line Doubler improves Video image quality
- Horizontal autolock scan frequency of 15-110 kHz
- RGB bandwidth of 120 MHz
- Vertical scan frequency of 37-200 Hz
- Displays all sources from VHS Video up to 1,600 x 1,200 pixel workstations

Specifiche tecniche

RETROGRAPHICS 808S

Specifiche generali	
Compatibilità	Display compatibility of from VHS Video up to 1600 by 1200 pixel workstations Horizontal autolock scan frequency of 15-110 kHz Vertical scan frequency of 37-200 Hz RGB bandwidth of 120 MHz Universal connection possibilities
Contrasto	>1000:1 (on full white / full black)
Emissione luminosa	1250 Nit / 364 ftL. (at 10 % peak white) 139 Nit / 41 ftL ANSI (Economy mode) 195 Nit / 57 ftL. ANSI (Normal mode) 214 Nit / 62 ftL. ANSI (Boost mode)
Dimensioni schermo	(diagonal) 67" (1.7 m)

Generato il: 08 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.

