

# BlendPRO-II

BlendPRO-II adds widescreen blending capability to the ScreenPRO-II family.



**Product specificaties****BLENDPRO-II****General specifications**

Video-ingang	Input Types: Four (4) Digital DVI channels per DDWG 1.0 on DVI-I connector Resolution: VGA up to UXGA @60 Hz (including all progressive HD resolutions and 1920x1200 and 2048x1080)
Video-uitgang	Four (4) high resolution channels Digital DVI channels per DDWG 1.0 on DVI-I connectors and Analog RGBHV on HD-15 connectors
Gebruikersbediening	Controlled from ScreenPRO-II controller via Ethernet
Fysiek	2 RU Rackmount Chassis
Ingangsvermogen	100-240 VAC, 50-60 Hz, 175 W max.
Milieuspecificaties	Temperature: 0-40 degrees C; Humidity: 0-95% non-condensing

Laatst bijgewerkt: 08 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.

[www.barco.com](http://www.barco.com)

**BARCO**