


Bragi

Using Barco's renowned Pulse electronic and software platform, Bragi is powered by a revolutionary, new, high lumens density (HLD) RGB LED light engine.



- Theater Series
- 4K UHD Resolution (3,840 x 2,160)
- Solid State RGB LED
- Up to 2,600 ANSI Lumens

Bragi takes its name from an historical ninth-century poet. His poems were so outstandingly artful and moving that subsequent generations imagined that, upon his death, Odin had appointed him the court poet of Valhalla.

Bragi, being Balder's brother and inherits the same design philosophy, optical core and lenses.

State of the art electronics

Our Pulse electronics are built on a superior FPGA platform featuring a dual core processor on the industry's only 20 nm SoChave, with 96 transceiver lanes delivering 3.3Tbps of serial bandwidth.

Thanks to our unique single step processing technology(SSPTM), Pulse electronics are designed to process 4K UHD, HDMITM 2.0a, HDCP 2.2 and HDR10 signals with extremely low latency.

Bragi uses the very latest 0.9" DMD DLP chipset, to display flawless 4K UHD (3,840 x 2,160 px) images.

LED Engine

Bragi uses a new optical engine, incorporating the best elements from previous models and combining them with new technologies, creating an even better optical engine.

Bragi's optical engine is not the only part that is redesigned, the light source is brand new, and this time it's not laser. The light source uses the very latest high lumens density (HLD), LED illumination technology.

HLD LED is unique in that it works around the 'law of etendue' (a property of light in an optical system, which characterizes how "spread out" the light is in area and angle...) to deliver a superb color experience and incredible brightness while enabling new levels of resolution.

RealColor

Combining HLD LED illumination with regular LED colors which appear more saturated, the human eye is tricked to interpret this as richer, brighter colors than they are physically measured. Bragi also includes a motorized DCI/P3 filter for improved HDR color accuracy.

Additionally, Barco's RealColor processing enables simple and accurate calibration to your desired color gamut or white point.

Product specificaties**BRAGI**

General specifications	
Type projector	Single chip DLP
Technologie	0.9" DMD™
Resolutie	3,840 x 2,160 (4K UHD)
Beeldverhouding	1.78:1
Lichtbron	Solid State RGB LED
Levensduur lichtbron	Up to 50,000 hours * Brightness mode dependent
Lichtuitvoer	Up to 2,600 ANSI Lumens
CLU (constante lichtuitvoer)	Yes
Contrastverhouding	1,800:1 Sequential 450:1 ANSI
Helderheidsuniformiteit	>90%
Lensbereik	(R9802232) -EN68 (0.30:1) -Periscope Lens (requires vertical installation) (R9801832) -FLDX UST (0.41:1) -90°ns (R9802244) -EN67 (0.65:1) (R9802243) -EN66 (0.80 - 1.21:1) (R9802003) -EN76 (0.95 - 1.30:1) (R9802242) -EN63 (1.20 - 1.70:1) * (R9802241) -EN61 (1.70 - 2.50:1) * (R9801211) -EN44 (2.50 - 4.60:1) * Standard Lens Option(s)
Optische lensverschuiving	Up to 88% vertical lens shift & up to 38% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Optische dowser	Yes
Kleurcorrectie	P7 RealColor™
Kleurenspectrum	REC.709 DCI (P3) via internal filter
Beeldverwerking	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Oriëntatie	360° Rotation
Netwerkverbinding	10/100 Ethernet via RJ45 connection
Geïntegreerde webserver	Yes
Diagnose	via Prospector web interface
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details
Ingangen	1 x HDMI™ 2.0 (HDCP 2.2) 1 x HDBaseT (HDCP 1.4 -9Gbps only) 2 x Dual Link DVI-D 2 x Display Port (1.2) 12G-SDI 1 x RJ45 Ethernet 1 x RS232 1 x Remote Control (RC) 3 x USB (2 x Rear, 1 x Front) DMX (1 x Input, 1 x Output)

Product specificaties**BRAGI**

Invoeresoluties	From VGA up to 4K UHD (3,840 x 2,160) @ 60Hz or up to 2,560 x 1,600 @ 120Hz
Latentie	TBD
Controle	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant NOTE: 12v Trigger(s) do not follow standard functionality and require an IP command to enable / disable them. Download our integration guide for more information.
Voedingsvereisten	100 -240V / 50 -60Hz
Energieverbruik	570 W -Max
BTU/uur	1,945 BTU/h -Max
Geluidsniveau (standaard bij 25°C/77°F)	30 -33 dB(A) Max.
Bedrijfstemperatuur	10 to 45 °C at Sea Level Optimal Set Point: 20 °C
Operationele vochtigheid	20 to 80% (relative humidity)
Luchtstroomvereisten	Air Inlet (from Rear w/Feet Down): Right Side Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 1cm Left: 1cm Right: 25cm Rear: 25cm Top: 1cm
Luchtuitstroom	58 ft ³ /min @ 22.9 °C 99 m ³ /hour @ 22.9 °C Download Lens & Airflow Data Here
Afmetingen (B x L x H)	Excluding lens 450 x 482 x 255 mm 17.7 x 19 x 10 in.
Gewicht	Excluding lens 21.5 kg / 47.4 lbs
Verzendingsafmetingen	Excluding lens 464 x 679 x 773 mm 18.27 x 26.7 x 30.4 in
Verzendgewicht	TBC
Standaardaccessoires	Power Cord, Remote Control
Certificeringen	CE, FCC Class A and cCSAus
Garantie	Limited 3 years parts and labor Extendable up to 5 years
24/7 operation	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
*	* Service required following 20,000 hours use Please contact an authorized Barco representative for details

Laatst bijgewerkt: 27 Mar 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.