

B-10

Barco's B-10 gets you out on the road - a cost-effective solution to really be any time, anywhere



Product specifications**B-10****General specifications**

LED display	Type	4x4 SLite 10 XP tiles (IP65 & TUV approved)	
	Dimensions (W x H)	3584 mm x 2688 mm (141.1' x 105.8')	
	Surface	9.6m ² (103.3ft ²)	
	Aspect ratio	4:3	
	Video processing	Rack-mounted LED-PRO	
	Content creation / sources	Not included	
	Equipped trailer	Total weight	3420 kg (7540 lb) - including tiles & generator
		Dimensions (W x H x D)	4240 x 2385 x 2080 mm (167' x 94' x 82') -excl. towbar
Safety speed for travelling		80km/h (49.7mi/h)	
Trailer & Lift	Lift	Hydraulic Ram	
	Lift raise	Bottom of display 2,5m (8.2ft) from the ground	
	Lift rotation	360 degrees, manual	
	Wind load	72 km/h (44.7mi/h)	
	Towbar	Adjustable in height	
Equipment rack	Dimensions	23 U	
Electrical	Case	Weather resistant	
	Generator	18KVA, diesel fueled, 28 hours of continuous operation at half load	
Packaging	Noise level	<68dB at 7m (23 ft)	
	Manuals	Building book + user manuals	
	Certificates	Compliance with CE standards + optional TUV	

Last updated: 10 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.