

# TLD (1.6 - 2.0)



**Product specifications****TLD (1.6 - 2.0)****General specifications**

Motorized Zoom	Yes
Motorized Focus	Yes
Throw Ratio	1.6 -2.0 : 1
Lens Shift Horizontal	On SLM G5/G8 Left 65% 65% Right
	On SLM R6/R8 Left 65% 65% Right
Lens Shift Vertical	On SLM G5/G8 Up 118% 20% Down
	On SLM R6/R8 Up 100% 20% Down

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.