

PDS-701 3G

Commutazione dello schermo low-cost di alta qualità



- Simple setup and operation
- Excellent price/performance ratio
- Simultaneous program output via DVI and analog connectors

The PDS series is designed to meet today's requirements for a high-quality, easy-to-use and fast seamless switcher with more digital inputs at an affordable price. Thanks to its straightforward setup and operation the PDS is a perfect fit for live events, boardrooms, hotel ballrooms, houses of worship, education and training facilities and fixed installations.

Program output

Il PDS-701 3G comprende due ingressi DVI-I, un 3G/HD/SD SDI e quattro ingressi analogici universali. All analog and DVI inputs support the EDID 1.3 specification. Users can capture and store up to three images that can be used as a LOGO source during the presentation. Built-in test patterns are also provided. Il PDS-701 3G offre un'uscita programma simultanea attraverso i connettori DVI e analogici.

The PDS series won a Commercial Integrator BEST Award at InfoComm 2013.

Processing

- Fast source acquisition
- Fast and seamless switching
- Auxiliary control from Encore and ScreenPRO-II controllers
- Up to three LOGO stores/recall capability
- Low video delay
- Software download via USB

Inputs

- All resolutions from NTSC/PAL up to WUXGA including all HD resolutions

- EDID support for analog and DVI sources
- DVI, analog, SDI 3G/HD/SD and BarcoLink
- HDCP 1.0 support for all DVI sources

Preview and program outputs

- All progressive resolutions from 480p up to WUXGA/HD
- DVI, analog, SDI 3G/HD/SD and BarcoLink
- Full screen outputs and PIPs
- Dual PIP mode
- 9x2 Matrix mode
- Zoom and Stretch fit modes
- Supports HDCP compliant displays
- Built-in test patterns
- Independent resolutions for program and preview outputs

Mechanical

- Auto ranging power supply
- Slim 1 RU height
- Width: 19" rack

Specifiche tecniche	PDS-701 3G
Specifiche generali	
Genlock	N/D
Uscita programma	1 uscita programma tramite HD-15, DVI o 3G-SDI
Uscite Aux scalate	N/D
Mixer	1 mixer o 2 pip
Ingressi video	7 ingressi fissi ■ 4 x analogici tramite HD-15 (connettore VGA) ■ 2 x ingresso DVI-I (supporta tecnologia sia analogica che DVI) ■ 1 x ingresso SDI 3G
Uscite video	1x DVI, 1x HD-15 (VGA), 1x 3G SDI
Memorizzazioni di fotogrammi	3
Effetti di strato	Transizioni di mixaggio e PIP a schermo intero
Multivisualizzatore	N/D
Espandibilità	N/D
HDCP	Conformità HDCP
Controllo	Ethernet RJ-45, computer con rilevamento automatico 10/100 Mbps, tablet, smartphone tramite browser web Le funzioni di controllo includono: configurazione dell'ingresso sorgente, selezione formato uscita, selezione modello test, selezione e controllo effetti di transizione
Manutenzione	Connettori DVI sostituibili sul campo
Dimensioni:	■ Altezza: 4,4 cm (1,78") - Montaggio su rack 1 RU ■ Larghezza: 48,26 cm (19 pollici) ■ Profondità: 36,2 cm (14,25 pollici)
Peso	5,67 kg / 12,5 lb
Alimentazione	Alimentazione in ingresso: 100-240 V CA 50/60 Hz 2a max.
Temperatura ambiente	0-40 °C / 32-104 °F
Umidità ambientale	0-95% senza condensa
Garanzia	3 anni per ricambi e manodopera

Generato il: 09 Jul 2024

© 2024 Barco nv. Tutti i diritti riservati. La riproduzione totale o parziale è proibita in assenza di autorizzazione scritta. Tutti i nomi di marchi e di prodotti sono marchi, marchi registrati o nomi commerciali dei rispettivi proprietari. A causa delle continue innovazioni, le informazioni e le specifiche tecniche sono soggette a modifiche senza preavviso. Controlla www.barco.com per le specifiche più recenti.

