

# iCon H600

Network-centric, 1080p HD, 6,000 lumens LCD projector



**기술 사양****ICON H600****일반 사양**

광 출력	6000 ANSI lumens
해상도	HD 1080 (1920x1080px)
밝기 균일도	> 95 % for the total screen
명암비율	> 800:1 (full white/full black)
디스플레이	3 x 1.65" polysilicon LCD panel with native HDTV resolution (1920 x 1080 pixels)
기능	<ul style="list-style-type: none"> <li>▪ AutoImage</li> <li>▪ Advanced picture-in-picture</li> <li>▪ Standard cable basket</li> <li>▪ Advanced digital zoom</li> <li>▪ Advanced Desktopintegration</li> </ul>
PIP(Picture-in-picture)	Background desktop image + up to 4 sources simultaneously (data or video)
입력	<p>Standard:</p> <ul style="list-style-type: none"> <li>▪ Layer 1: RGBHV or Component input; Composite video input; S-Video input</li> <li>▪ Layer 2: RGBHV or Component input; Composite video input; S-Video input</li> <li>▪ Layer 3: DVI input and D15 input</li> <li>▪ Layer 4: Available for optional inputs</li> </ul> <p>Optional:</p> <p>The following input boards can be placed on any of the 4 layers:</p> <ul style="list-style-type: none"> <li>▪ RGBHV or Component input; Composite video input; S-Video input</li> <li>▪ DVI input and D15 input</li> <li>▪ SDI and HDSDI input and loop trough</li> </ul>
출력	DVI out (1920 x 1080 at 60 Hz) of full screen composed image (including window inserts)
통신	<ul style="list-style-type: none"> <li>▪ 1x RS-232C (D-9 connector)</li> <li>▪ mini-jack for wired remote control</li> </ul>
호환성	<ul style="list-style-type: none"> <li>▪ All current video sources</li> <li>▪ All current HDTV sources</li> <li>▪ All computer graphics sources with a pixel clock up to 275 Mhz (VGA, XGA, SXGA, SXGA+, UXGA, QXGA:2048x1536)</li> <li>▪ DVI up to UXGA and HDTV resolution</li> <li>▪ HD-SDI, SDI optionally available</li> </ul>
입력 소스 호환	2048 x 1536 @ 56Hz max input
스크린 크기	From 1-6m / 3-20ft.
스캔 주파수	Horizontal 15kHz -110 kHz Vertical 25 Hz -150 Hz
네트워크 연결	2 x 10/100/1000 Base-T Ethernet
온보드 디스플레이 서버	<ul style="list-style-type: none"> <li>▪ Provides native 1920 x 1080 resolution</li> <li>▪ Pentium 4 2,6 Ghz, 1 Gigabyte DDR RAM, 40 Gigabyte harddisk (upgradeable)</li> <li>▪ 2 x PCMCIA slot for Wireless LAN cards, memory cards, extensions for inputs and outputs, Bluetooth</li> <li>▪ 2 USB connectors and PS2 connector</li> <li>▪ 2 x 10/100 Mb/s Ethernet RJ 45 connector</li> <li>▪ 1x RS-232C (D-9 connector)</li> <li>▪ Included software:</li> </ul>
주위 온도	5°C up to 40°C
램프	2 x 300 Watt UHP lamp Lifetime: 1500 h/lamp

## 기술 사양

## ICON H600

렌즈	<ul style="list-style-type: none"><li>• Fixed lenses:<ul style="list-style-type: none"><li>-QGD (0.86:1) R9840491</li><li>-QFD (1.27:1) R9840400</li><li>-QFD (2.5:1) R9840290</li><li>-QFD (7.0:1) R9840410</li></ul></li><li>• Zoom lenses:<ul style="list-style-type: none"><li>-QHD (1.4 -2.0:1) R9849930</li><li>-QHD (2.1 -3.0:1) R9849810</li><li>-QFD (3.4 -4.5:1) R9840060</li><li>-QFD (4.5 -6.0:1) R9840100</li></ul></li></ul>
렌즈범위	Vertical: -120% to +120% Horizontal: -50% to +50%
먼지 필터	Dense High Quality Microfilter (front side removeable)
소음도	< 39 dB
기본 전압	90V-255V
전력 소비	Max. 900 Watt
소비 전력	Max. 2900 BTU/hour
AC 전원	90V -255V (50 Hz -60Hz)
무게	35 kg (77 lbs)
크기	D x W x H, without cable basket: 679 x 567 x 282 mm (26.73 x 22.32 x 11.10 inch)
안전 규정	Compliant with UL1950 and EN60950
전자파 장애	Compliant with FCC rules & regulations, part 15 Class A, CE EN55022 Class A and CCC

### 작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 [www.barco.com](http://www.barco.com)을(를) 확인하세요.