

Atlas67.C4DLP



技术规格

ATLAS67.C4DLP

一般规格

电源	100-240 VAC, 50-60 Hz, 1.6-0.7A
兼容性	Barco's Atlas integrates with the existing network environment and video sources via BARCO's graphical control units: EOS Compact, Power and Ultra, Hydra and Visu+.
对比度	XGA -350:1 (full field contrast)
尺寸结构	<ul style="list-style-type: none">· Width 1368 mm / 53.86 in.· Height 1026 mm / 40.39 in.· Footprint 753 mm / 29.65 in.· Depth 897 mm / 35.32 in.· Socket height (min) 614 mm / 24.17 in.· Socket height (max) 1288 mm / 50.70 in· Weight 130 kg / 238.1 lbs
运行环境	<ul style="list-style-type: none">· Operating temperature: 17 °C -27 °C or 62 °F -80 °F (stitched screen) 0 °C - 40 °C or 30 °F - 105 °F (screen module)· Humidity: 40% -60%, non condensing (stitched screen) max 80%, non condensing (screen module)
灯泡	120 Watt UHP™ lamp
亮度	XGA -100 cd/m ²
可选	All projector settings are accessible through Barco's wall management software. Full features of this software can be viewed under this website 'Application software'
功率消耗	XGA -160 W
分辨率	XGA -1024x768 pixels
屏幕尺寸	<ul style="list-style-type: none">· 67" diagonally· High contrast black type screens for wide viewing angles· Other screens on request

生成于: 08 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。