

DICOM Theater Lite

First-class performance in a compact design



Product specifications

DICOM THEATER LITE

General specifications

Technology	<ul style="list-style-type: none">single chip DLPDMD with DarkChip
Native resolution	1400 x 1050 pixels
Light output	2000 Ansi Lumen
Contrast	2000:1 (full white / full black)
Lamp type & power	250W UHP
Lamp lifetime	<ul style="list-style-type: none">2000 hrs (full power)4000 hrs (dimmed, economy)
Lens offset	8% of image height (fix)
Throw Ratio	1.7-2.2:1 (standard)
Orientation	Landscape
DICOM factory presets	<ul style="list-style-type: none">DICOM full white / full white boostDICOM ClearBase / ClearBase boost
DICOM calibration	<ul style="list-style-type: none">TheaterWatchVisual DICOM calibration tool
Digital Video Input	1 x DVI-D (Single link)
Analog video inputs	<ul style="list-style-type: none">2 x VGA (15-pin HDBSUB)1 x Composite video (3 x RCA)1 x S-Video (4-pin Mini DIN)1 x Composite video (RCA)
Computer output	1 x VGA (15-pin HDBSUB)
Communication	<ul style="list-style-type: none">2 x R232 (In / Out on 9-pin DSUB)1 x LAN (TCP/IP network on RJ45)1 x USB (mouse control)
Audio Input	2 x Stereo (data / video on 3.5mm mini jack)
Audio output	1 x Stereo (3.5mm mini jack)
Horizontal scan frequencies	15 -150 kHz
Vertical scan frequencies	48 -190 kHz
Computer graphics formats	<ul style="list-style-type: none">VGA, SVGA, XGA, SXGA, SXGA+, UXGADVI sources up to SXGA+
Video formats	<ul style="list-style-type: none">PAL, SECAM, NTSC 3.58, NTSC 4.43HDTV (1080i, 720p, 576 i/p, 480 i/p)
Power Dissipation	1480 BTU/hr
Power requirements	100 -240 VAC, 50 to 60 Hz
Power consumption	350 Watt
Safety	UL1950, EN60950
Electromagnetic Interference	FCC Class A, ICES-003 Class A, EN55022 Class A
Other approvals	CCC, CE
Dimensions	244 x 278 x 88 mm (9.6 x 10.9 x 3.5 inch) (LxWxH)
Weight	3.4 kg / 7.5 lbs
Operation noise	28 dB(A)
Standard accessories	<ul style="list-style-type: none">Cable basketIR remote control with laser pointer

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.