

Mono 15



Product specifications**MONO 15****General specifications**

Calibrated Brightness	2100 nits
Contrast ratio	1000:1
Physical Resolution	15 mm
Hor. viewing angle	140°
Vert. viewing angle	75°
Optimal viewing distance	20 meter
Weight	11.4 kg / m ²
Avg Power Consumption	.07 Watt (per pixel)
Max. power consumption	.17 Watt (per pixel)
Temperature range	Operating: -20°C <> 40°C Storage -20°C <> 60°C
Outdoor Compliance	IP 54
Screen size	Unlimited
Lifetime	100.000h [half brightness]
Processing	13 bit

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.