


Loki CinemaScope

Offering the same UHD enhancements as the Loki projector, coupled with a high-capacity 2.37:1 aspect DLP engine.



- Theater & Media Room Series
- 5K UHD Resolution (5,120 x 2,160)
- Laser Phosphor
- Up to 7,800 ANSI Lumens

Loki CinemaScope's exceptional design allows a cinemascope film to be shown without requiring an anamorphic lens. The projector also provides Barco's renowned single-step processing (SSPTM) and low latency scaling technologies.

Professional grade optics

By basing Loki CinemaScope on a proven optical architecture, custom designed aspherical glass elements and enhanced low dispersion glass lenses, image quality is in a class of its own. Contrast is not only increased, but the details within the darkest parts of the image are more visible.

CinemaScope

Our unique aspect ratio detection system, automatically crops and scales content to fit the appropriate screen area, ranging from 1.78:1 to 2.39:1.

Manual cropping is also available for custom configurations such as cinemascope subtitle support, where only the top black bar is removed from none 1.78:1 content, preserving the subtitles at the foot of the image.

Laser light source

Outstanding image quality requires an exceptional light source, which is why Loki CinemaScope uses our brand-new dual laser engine.

Alongside significantly improved image uniformity, lasers last longer than traditional projector lamps, offer great image quality consistency over their lifetime, are less fragile and offer near instant on/off performance.

Liquid cooling

Loki CinemaScope has departed from a pure fan based cooling system, opting instead for a liquid cooling PID regulation system. This combined with our simulation grade warp engine allows Balder to operate at any angle (free rotation), offering new possibilities when it comes to architectural integration.

Spécifications techniques

LOKI CINEMASCOPE

Spécifications générales

Type de projecteur	Single chip DLP
Durée de vie de la source lumineuse	20,000 - 60,000 hours Laser intensity dependent
CLO (rendement lumineux constant)	Yes
Coupe-flux optique	Yes
Technologie	0.9" DMD™
Serveur Web intégré	Yes
Résolution	5,120 x 2,160 (5K UHD)
Diagnostic	via Prospector web interface
Rapport d'aspect	2.37:1 (CinemaScope)
Source de lumière	Laser phosphor
Luminosité	DCI (P3) Color Wheel: Up to 5,100 ANSI lumens T Color Wheel: Up to 6,500 ANSI lumens M Color Wheel: Up to 7,800 ANSI lumens
Rapport de contraste	1,800:1 Sequential 450:1 ANSI
Uniformité de la luminosité	>90%
Résolutions d'entrée	From VGA up to 4K UHD (3,840 x 2,160) @ 60Hz or up to 2,560 x 1,600 @ 120Hz
Gamme de lentilles	(R9802232) -EN68 (0.30:1) -Periscope Lens (requires vertical installation) (R9801832) -FLDX UST (0.41:1) -90°ns (R9802244) -EN67 (0.65:1) (R9802243) -EN66 (0.80 - 1.21:1) (R9802003) -EN76 (0.95 - 1.30:1) (R9802242) -EN63 (1.20 - 1.70:1) * (R9802241) -EN61 (1.70 - 2.50:1) * (R9801211) -EN44 (2.50 - 4.60:1) * Standard Lens Option(s)
Latence	TBD
Décalage de lentille optique	Up to 122% vertical lens shift & up to 40% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Correction de couleur	P7 RealColor™
Alimentation veille	Standby ECO Mode: 110v -0.78W (with LAN Connection) 230v -0.87W (with LAN Connection)
Espace colorimétrique	DCI (P3) Color Wheel: DCI P3 T Color Wheel: REC.709 M Color Wheel: REC.709
Traitement des images	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Orientation	360° Rotation
Connexion réseau	10/100 Ethernet via RJ45 connection
Humidité de fonctionnement	20 to 80% (relative humidity)
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details
Entrées	1 x HDMI 2.0 (HDCP 2.2) 1 x HDBaseT (HDCP 1.4 -9Gbps only) 2 x Dual Link DVI-D 2 x Display Port (1.2) 12G-SDI 1 x RJ45 Ethernet 1 x RS232 1 x Remote Control (RC) 3 x USB (2 x Rear, 1 x Front) DMX (1 x Input, 1 x Output)
Dimensions de l'envoi	Excluding Lens 720 x 910 x 630 mm 28.4 x 35.8 x 24.8 in.
Contrôle	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant NOTE: 12v Trigger(s) do not follow standard functionality and require an IP command to enable / disable them. Download our integration guide for more information.

Spécifications techniques

LOKI CINEMASCOPE

Température du stockage	-20 to 60 °C
Poids d'expédition	Excluding Lens 55kg / 121.3 lbs
Humidité de stockage	10 to 90% (relative humidity)
Consommation d'énergie requise	100 -240V / 50 -60Hz US Requires: 20A Service (NEMA 5-20P Plug Type)
Accessoires standards	Power Cord, Remote Control
Certifications	CE, FCC Class A and cCSAus
Consommation électrique	2180 W -Maximum
Niveau sonore (typique à 25 °C)	38 dB(A)
Fonctionnement 24h/7j	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
Température de fonctionnement	10 to 45 °C at Sea Level Optimal Set Point: 20 °C
*	Firmware upgradable Please contact an authorized Barco representative for details
BTU par heure	Max. 6,000 BTU/h
Exigences en matière de débit d'air	Air Inlet (from Rear w/Feet Down): Right Side Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 1cm Left: 1cm Right: 50cm Rear: 100cm Top: 1cm
Débit d'air d'échappement	193 ft ³ /min @ 25 °C 327 m ³ /hour @ 25 °C Download Lens & Airflow Data Here
Dimensions (P x L x H)	Excluding Lens 577 x 738 x 304 mm 22.7 x 29.1 x 12 in.
Poids	Excluding Lens 44.5 kg / 98.1 lbs
Garantie	Limited 3 years parts and labor Extendable up to 5 years
Exigences de sécurité	This projector is Risk Group 2 (RG2) according to IEC EN 62471-5. This projector may become Risk Group 3 (RG3) when an interchangeable lens with throw ratio greater than 3.15 is installed. For Northern America, installation requirements according to Risk group 3 (RG3) must be followed when interchangeable lens with throw ratio greater than 2.33 is installed. Refer to the installation manual for further information.

Créé le : 29 Jan 2025

© 2025 Barco nv. Tous droits réservés. La reproduction partielle ou intégrale sans autorisation écrite préalable est interdite. Les noms de marques ou de produits sont des marques commerciales, des marques déposées ou des appellations commerciales appartenant à leurs détenteurs respectifs. Pour des raisons d'innovation continue, les informations et les caractéristiques techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter www.barco.com pour les dernières spécifications.

www.barco.com

BARCO