

ClickShare X-Display Plus 65"

ClickShare X-Display Plus, designed around your laptop (BYOM), integrates advanced audio, video, and display capabilities to deliver a seamless hybrid meeting experience.



*可立享无线会议屏内置 CX-M 模块和可立享按钮1个

- **16 Microphone array with a 12-meter range for precise audio capture**
- **AI-driven noise reduction, AI sound masking, and echo cancellation**
- **High-quality, immersive stereo sound**
- **4K 50-megapixel ultra-clear camera**
- **400nits high-brightness anti-glare display for clear visibility**
- **Expandable with a variety of third-party peripherals**
- **Built-in ClickShare CX-M module**

ClickShare X-Display Plus is an innovative all-in-one solution that seamlessly combines audio, video, display, and collaboration tools, designed for hybrid work environments. Equipped with a 16 Microphone array and a 4K 50-megapixel high-definition camera, it delivers an exceptional audio-visual experience. It supports compatibility with major cloud platforms and devices, allowing effortless switching between MTR and BYOM modes. With wireless plug-and-play connectivity, setup is simple and intuitive. It also provides enterprise-level data security and remote management features, ensuring a reliable and efficient meeting experience.

Product specifications**CLICKSHARE X-DISPLAY PLUS 65"**

Display	
Size	65-inch
Type	LCD
Resolution	4K UHD (3840*2160)
Contrast ratio	4000:1
Brightness	400 cd/m2 [typical]
Color gamut	94% P3 [typical]
Color accuracy	ΔE
Backlight type	D-LED
Panel	<ul style="list-style-type: none">• Anti-glare• Anti-ambient light interference, Clearer display
Refresh Rate	60Hz
Camera	
Pixels	50 MP
Sensor source	SONY
Resolution	4K, 1080p, 720p at 30fps
FOV	99°
Pixel size	1.0 μm
ZOOM	5x digital zoom
WDR	Yes
Distortion correction	Yes
Lens cap	Manual slide cover
AI function	
Group Framing	Yes
Composition mode	Yes [up to 8 people]
Speaker framing	Yes
Intelligent tracking	Yes [Speaker framing with panoramic view]
AI soundscreen	Yes [30°/60°/90°/180° -4 level available]
Speaker AI adaptive	Yes [According to the different acoustic environment of the meeting space, the sound effect of the Speaker is automatically adjusted to fit the current meeting space]
Microphone	
Quantity	16 beamforming MEMS microphones
Hardware accelerated audio processing	Yes
Pickup distance	up to 12 meters
Sound pickup angle	180°
Echo cancellation	Yes
Noise suppression	Yes [More than 300 types of noise can be suppressed]
Automatic gain control	Yes
Dereverberation	Yes
Speaker	
Channel	2.1 Channel stereo
Quantity	5 Speaker units (separate bass speakers)
Frequency Domain	60 Hz to 20KHz
Output Power	2x15W+20W
Position	Top
General specifications	
Dimensions (W*D*H)	1465.1*77.7*912mm
Weight	35.185 kg [gross weight] 30.19 kg [net weight]
Expansion capability	
Support extend Microphone (Cascade mode)	Yes [up to 4 ClickShare Wireless Speakerphone]
Third-party USB peripherals	Yes
OPS	CX-M [included]
Connections	
HDMI IN	2 [HDMI 2.0]
HDMI OUT	1 [1080p / 2160p]
USB-C (front)	1 [front]
USB-C (board)	1 [board]
USB-B (2.0)	1
USB-A (3.0)	2
USB-A (2.0)	1 [only for X-Display upgrading]
RJ45 (MIC IN)	1 [connect to ClickShare Wireless Speakerphone]
Audio Out	1 [SPDIF]

Product specifications**CLICKSHARE X-DISPLAY PLUS 65"**

RS232	1 DB9, 1
RJ45 (1Gbps)	2 Ethernet
Accessories	
Cable	Power cord x 1
Remote control	1
Wall-mounted bracket	Yes
Floor stand	Optional
Storage Box	Yes
Type-C Cable	Yes
Power	
Power Supply	AC100 to 240V, 50/60Hz
Power Cord	China, length 3Meters
Max Operating Power Consumption	< 180W
Max Standby Power Consumption	< 0.5W
Environment	
Operation Temperature	0°C~40°C
Operation Humidity	10% ~ 90% RH
Storage Humidity	10% ~ 90% RH
Storage Temperature	-20°C~60°C
Altitude	5000metres
Compliance	
EMC/Safety	CCC/CE
Energy	China Energy Label 2
RoHS	China RoHS
CX-M Specifications	
Video Outputs	4K UHD (3840*2160) @ 30Hz. HDMI 1.4b(OPS 80pins connector) or USB-C DisplayPort 1.2
Audio output	USB
USB	1 X USB-C
ClickShare Buttons	1
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast
Maximum sources simultaneously on screen	2
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-50°C
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHZ and 5 GHz
Connections	1x Ethernet LAN 1Gbit 1x USB-C 3.0 (front) br> 1x OPS-80 pin
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 40°C (104°F) at 5000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	NA
Certifications	SRRC/CE
Touch screen support & Interactivity	Yes
Local view	Yes
Wireless conferencing	via App or Button
Network connection	LAN & WiFi
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage upon registering via SmartCare
Dimensions (HxWxD)	202mm x 119mm x 30mm
Power consumptions	Operational: 5-10W, 16W Max
Power Supply	18V DC from OPS display
Weight	698g

Last updated: 16 Apr 2025

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.