


NX6 (fixed installation)

6mm pixel pitch, 2,000 nits, true black indoor LED display



Thanks to its black LED, the NX6 delivers more contrast and deeper black levels than any other product on the market. Black LED is only one element that makes the NX6 unique. Key advances in base materials, mechanical design and color processing have raised the bar of LED displays to new heights of image quality.

- Phenomenal black levels
- 4,200:1 contrast ratio
- 2,000 nits brightness
- 16-bit color processing
- Replaceable shaders
- Consistent uniformity
- High Definition-ready
- Modular creativity

Product specificaties

NX6 (FIXED INSTALLATION)

General specifications	
Pixelpitch	6.22 mm
Helderheid	2,000 nits
Led-configuratie	3-in-1 SMD
Pixeldichtheid	25,829/sqm 2,402/sqf 5,832/tile (72x81)
Hor. kijkhoek	120°
Vert. kijkhoek	+60°, -60° (@ 50% brightness)
Contrastverhouding	4,200:1 (at 500 lux)
Levensduur	60,000 hours to 75% of initial brightness
Energieverbruik	219 W/tile (max) 104 W average
Netspanning bij gebruik	200-240V / 50-60Hz
Paneelafmetingen	Width: 448mm (17.6") Height: 504mm (19.8") Depth: 228.6mm (9")
Gewicht / tegel	13.8 kg/30.3 lbs
IP-classificatie	Indoor use only

Laatst bijgewerkt: 10 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

